

STILE 550S-WH

Cardioid Gooseneck Microphone with Switch – 55cm length, White

STILE 450-550 Series Goose-neck Microphones deliver high-level performance, control, and flexibility for meetings and conferences.

High quality cartridges with **cardioid polar pattern** deliver accurate voice capture with **minimum pickup of room noise**.

Dual bend at bottom and top allow precise placement in meetings and conferences. A choice of 45 cm (17.7 inch) and 55 cm (21.6 inch) lengths, with or without on/off switch, match different table dimensions or seating configurations.



PRODUCT DETAILS

Key features

55 cm (21.6 inch) lengths, white finish

On-Off switch with Led indicator

Designed for high-quality sound capture in meetings and conferences

Reference sound-receiving distance 30-40 cm

Gooseneck bends at bottom and top

Accept Phantom Power from 9V to 52V

Foam windscreen included

Works with STILO B200/S mic bases

Specifications

Element	Condenser (Back Electret)
Polar pattern	Cardioid (Direzionale)
Reference sound-receiving distance	30-40 cm
Frequency response	50Hz-18kHz
Sensitivity	-45dB (1v @ 1pa)
Impedance	600ohms
Max input SPL	123dB (1kHz @ 1% T.H.D)
S/N ratio	70dB, 1kHz @ 1pa
Phantom power requirement	9-52V DC
Microphone Size	550 x Ø13mm
Microphone Weight	130g
Wind-screen size	40 x Ø32mm
Packing Size	600 x 30 x 30mm
Packing Weight	0,16kg