

STILE 350H

Cardioid Gooseneck Microphone - 35cm length, Black

STILE 350H Mini-shotgun **Cardioid** Microphone deliver high-level performance, control, and flexibility for meetings and conferences.

Its high-quality cartridge with cardioid polar pattern delivers good control in difficult acoustic conditions. The result is **superior voice capture** and **lower pickup of room noise** compared to other standard cardioid goose-neck microphones. The **bend at bottom** allows precise placement in meetings and conferences.



PRODUCT DETAILS

Key features

35 cm (13.78 inch) length, black finish

Designed for high-quality sound capture in meetings and conferences

50m Reference sound-receiving distance

Gooseneck bend at bottom

Accept Phantom Power from 9V to 52V

Foam windscreen included

Works with STILO B200/S mic bases

Specifications

Element	Condenser (Back Electret)
Polar pattern	Cardioid
Gooseneck length	350mm
Reference sound-receiving distance	50cm
Frequency response	50Hz - 20kHz
Sensitivity	-43 dB \pm 1 dB (0dB=1V/Pa @ 1kHz)
Output Impedance	600 Ω
Max input SPL	123 dB (1 kHz @ 1% T.H.D)
Phantom power requirement	9V - 52 V DC, 3 mA typical
Microphone Size	350 x \varnothing 12 mm
Wind-screen Size	150 x \varnothing 22 mm
Microphone Weight	60g
Packing Size	397 x 68 x 33,8 mm
Packing Weight	0,15 kg