



Lumina Floor Lamp

The Lumina Floor Lamp is a sturdy lamp with a long and flexible goose neck.



A modern minimalist design with five brightness levels on five different colour settings, adjustable by touch on the lamp pole or using the remote control, it is ideal for crafters, mobile beauty, reading and users with low levels of vision.

The lamp provides a long reach when required but can easily be adjusted to a shorter length by bending the goose neck.

It comes with a remote control for light adjustment giving the user the ability to adjust both the brightness and colour temperature, as well as turning the light on and off.

FEATURES

- Flexible goose neck, enables bright light to shine where needed.
- Bright LEDs provide daylight simulation.
- 5-step dimmer, with 5 different levels of light temperature.

TECHNICAL DETAILS

- Colour temperature: 2800K, 4000K and 6500K.
- Head size: 180cm (71 inches).
- Base plate diameter: 22cm (8.5 inches).
- Total weight: 2.55kg.
- Cable length: 190cm (75 inches).
- Colour: White & Black.
- Comes with a 2 year warranty.



Remote control



Flexible gooseneck



5 brightness settings



Colour Temps
2800K, 4000K, 6500K

Telephone 0117 370 9995 Email sales@native-lighting.com
For more information visit www.native-lighting.com