

Chameleon Magnifier Lamp

The Chameleon Magnifying Lamp has 3 colour settings and 1.75X magnification.

This lamp has 3 different colour temperatures ranging from 2700K, 4000K, 5500K and each colour temperature also has three brightness levels, ensuring the user always has the optimal level of light for working on any task.

The glass lens can be protected by a cover which is supplied and designed to guard the lens against dust and scratches.

The stable flexible arm on the lamp is covered, making it ideal for cleaning. The lamp has a long reach of 120cm (47 inches).

This magnifying lamp comes with a clamp, which enables it to be locked to desks, benches, beauty beds and any flat surface.



FEATURES

- Bright LEDs provide daylight simulation.
- 3 brightness levels available for each colour temperature.
- High quality 17cm (7") glass lens with 1.75X magnification (3 diopter)
- Flexible arm to ensure the user can work freely around the lamp.

TECHNICAL DETAILS

- 3 colour temperatures: 2700K, 4000K, 5500K.
- Lux output at 15cm (6): 5,000 Lux.
- Lens Size: 17cm (7").
- Lamp diameter: 25cm (10 inches).
- Reach: 120cm (47 inches).
- Clamp depth: 7.3cm (3 inches).
- Weight: 2.57kg.
- Colour: White.
- Comes with 2 year warranty.



1.75X
Magnification



3 brightness
settings



Clamp
fixing



Bright
LEDs

Telephone 0117 370 9995 Email sales@native-lighting.com
For more information visit www.native-lighting.com