



### Product Highlights:

- Upgrade your laptop or desktop computer for faster startups, data transfers, and application loads<sup>1</sup>
- Experience better performance and reliability than a traditional hard drive<sup>2</sup>
- Shock and vibration resistant with no moving parts<sup>3</sup>
- Three-year limited warranty

### Capacities:

**240GB**  
(up to 550MB/s read<sup>1</sup>)

**480GB**  
(up to 550MB/s read<sup>1</sup>)

**960GB**  
(up to 550MB/s read<sup>1</sup>)



## Boost your computer's performance

Improve your existing system's performance with the Lexar® NQ100 2.5" SATA III (6Gb/s) SSD. This easy upgrade gives you faster boot-ups, application load times, and data transfers with read speeds of up to 550MB/s<sup>1</sup>. The NQ100 SSD is shock and vibration resistant<sup>3</sup>, and features no moving parts, making it cooler, quieter, and more energy efficient than a traditional hard disk drive. Available in capacities from 240GB to 960GB, the NQ100 will rejuvenate your current laptop or desktop. Three-year limited warranty.

**Impressive speeds with a simple upgrade.** With the NQ100 SSD you can save time and improve your computer's performance with read speeds of up to 550MB/s<sup>1</sup>. It will make boot-ups, data transfers and application load times a breeze.

**Rejuvenate your laptop or PC.** Leave the performance anxiety of using a traditional hard drive behind you, and enjoy faster speeds and extended storage space with the NQ100 SSD<sup>2</sup>.

**Built to last.** Unlike traditional hard disk drives, the NQ100 SSD has no moving parts, so it's more durable. Add to that, it's shock and vibration resistant and you've got one robust and reliable SSD to safely store and render your large-sized data, photos, and 4K videos<sup>3</sup>.

**Rigorously tested.** All Lexar product designs undergo extensive testing in the Lexar Quality Labs, facilities with more than 1,100 digital devices, to ensure performance, quality, compatibility, and reliability.

*For more than 20 years, Lexar has been trusted as a leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, and solid-state drives. With so many options, it's easy to find the right Lexar solution to fit your needs. Lexar products are available worldwide at major retail and e-tail stores. For more information or support, visit [www.lexar.com](http://www.lexar.com).*

<sup>1</sup> Up to 550MB/s read transfer, write transfer speeds lower. Speeds based on internal testing. Actual performance may vary.

<sup>2</sup> Comparison based on internal testing. Actual performance may vary.

<sup>3</sup> Shock resistant (1500G, duration 0.5ms, Half Sine Wave) and vibration resistant (7~800Hz, 3.08Grms, 20G, 1 Oct/min, 30min/axis(X,Y,Z)). Based on internal testing. Actual performance may vary.

Lexar is not liable for any loss of data or images.

#### NOTE:

Security safeguards, by their nature, are capable of circumvention. Lexar does not guarantee data will be 100% secure from unauthorized access, alteration, or destruction.

Product appearance, performance, software offerings, and packaging may vary depending on ship date and available inventory.

Actual usable memory capacity may vary. 1GB equals 1 billion bytes.

[www.lexar.com](http://www.lexar.com)

©2020 All Rights Reserved. Information, products, specifications, and features are subject to change without notice. Neither Lexar nor Longsys is responsible for omissions or errors in typography or photography. Lexar, the Lexar logo, and all other Lexar trademarks are the property of Longsys Electronics (HK) Co., Ltd. or Shenzhen Longsys Electronics Co., Ltd. All other trademarks are property of their respective owners.