



SUREFIRE



KINGPIN M1 60%

GAMING
KEYBOARD



PART NUMBER:

48712/13/14/15/16/17



FORM FACTOR
60%



MECHANICAL
RED SWITCHES



LIFESPAN
50 MILLION HITS



ADJUSTABLE SETTINGS
VIA SOFTWARE*

- 🔥 60% gaming keyboard with RGB backlighting
- 🔥 Mechanical red linear switches – 1ms response time
- 🔥 50 million key presses lifespan
- 🔥 Multi-optional RGB lighting – 6 active modes
- 🔥 100% anti-ghosting keys and 3 multimedia shortcut keys
- 🔥 Adjustable settings via software*

PACK CONTENT

SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard
Quick Start Guide



* Download at www.surefire-gaming.eu/support
(for Windows only)

surefire-gaming.com



SUREFIRE



COMPACT FOR MORE SPACE

KingPin M1 is ideal for streamlined setups where desk space is a premium. Perfect for taking to events, LAN parties or tournaments. The powerful software allows gamers to set functions for every key, create and manage macros, and disable keys for improved game play.

LIGHTNING FAST

The red mechanical switches have a linear travel, combined with minimal spring force, resulting in a silky-smooth keypress that's ideal for performance gamers. With a superfast 1ms response time and 50 million keystrokes guaranteed, the SureFire KingPin M1 will not let you down.



60% FORM FACTOR

The KingPin M1 delivers all the functionality of a regular gaming keyboard compressed neatly to 60%. Yet it loses no functionality because all missing inputs are still accessible via secondary functions and shortcuts. For all those gamers who prefer minimalistic and compact set ups – you know who you are!

LIGHT UP THE PARTY!

The stunning RGB lighting in the SureFire KingPin M1 offers a multitude of colour options that can be programmed in with the software supplied. With 6 active lighting modes including a customised option, and adjustments for speed and intensity, players can set the lighting ambience to match the game scenario and bring everything to life.



GENERAL

Dimension (LxWxH)	293 x 104 x 42 mm	Weight	610 g
Size Type	60%	Height	Adjustable - 2 positions
Product Material	Ultra-resistant ABS		

INTERFACE

Connection Type	Wired	Connector Type	USB-A
Cable Length	1.8 m	Cable Type	Braided

KEYBOARD

Key Technology	Mechanical	Switch Type	Red Mechanical Switches
Key Operating Force	50+/-10g	Lifetime of Keys	50 Million Hits
Response Time	1ms	Key Travel	4±0.4mm
Keyboard Rollover	100% Anti-ghosting keys	Multimedia Keys	3 Multimedia shortcut keys

LIGHTING

Adjustable	Yes	LED	RGB backlight
Settings	6 active modes (5 RGB modes and 1 customisable mode): Flowing; Colourful breathing; One click; Ripple; Single colour breathing (choice of 8 colours and light off); Customised. Adjustable light intensity – 16 levels. Adjustable speed – 16 speeds		

COMPATIBILITY

Software Platforms	Windows, Mac OS, Chrome OS	Device Types	PC, Laptop, Gaming console with USB-A port
---------------------------	----------------------------	---------------------	--

SYSTEM REQUIREMENTS

OS	Windows 11, 10, 8, 7 Mac OS X 10.6 or higher	Connection	USB 3.2 Gen 1 or USB 2.0 Consoles with USB-A Port
-----------	---	-------------------	--

OPERATIONAL CONDITIONS

Operating Temperature	-5°C to 45°C	Storage Temperature	-20°C to 60°C
Operating Humidity	10% to 80% RH	Voltage range	5V/260mA (max)

* Download at www.surefire-gaming.eu/support
(for Windows only)

ORDERING INFORMATION

P. No.	Description		
48712	SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard QWERTZ German	Barcode	023942487128
		EAN128 (outer)	(02)00023942487128(37)05(91)485
		EAN14 (outer)	50023942487123
48713	SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard QWERTY US English	Barcode	023942487135
		EAN128 (outer)	(02)00023942487135(37)05(91)485
		EAN14 (outer)	50023942487130
48714	SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard QWERTY Nordic	Barcode	023942487142
		EAN128 (outer)	(02)00023942487142(37)05(91)485
		EAN14 (outer)	50023942487147
48715	SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard QWERTY Spanish	Barcode	023942487159
		EAN128 (outer)	(02)00023942487159(37)05(91)485
		EAN14 (outer)	50023942487154
48716	SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard QWERTY Italian	Barcode	023942487166
		EAN128 (outer)	(02)00023942487166(37)05(91)485
		EAN14 (outer)	50023942487161
48717	SureFire KingPin M1 60% Mechanical RGB Gaming Keyboard AZERTY French	Barcode	023942487173
		EAN128 (outer)	(02)00023942487173(37)05(91)485
		EAN14 (outer)	50023942487178

WARRANTY

2 Years