

MOOD 1818WP

18x18W RGBWA+V 6in1 LED PAR Light for Outdoor use (IP65)

Especially designed for outdoor use thanks to the **IP65 protection degree**, Centolight MOOD 1818WP is the right choice for **architectural or live applications** when a compact yet powerful and silent projector is required. It offers a complete color palette thanks to the **6in1 LED technology**, which provides Red, Green, Blue, White, Amber and Violet basic colors. The accurate and smooth color mixing, the 6CH/7CH/10CH DMX control mode, the Master/Slave, Auto, and Sound Active modes make this fixture extremely versatile. **Power and DMX connections** are completely **waterproof** to ensure maximum protections to rain and mud infiltration.



PRODUCT DETAILS

Key features

Made to resist to rigors of external weather conditions

Suitable for outdoor architectural and live applications

IP65 protection degree with waterproof connectors

Totally silent operation

DMX512 protocol, Master/Slave mode, Sound Active mode, Auto Run mode

Light source 18x18W RGBWA+V 6in1 long life-span LED

Light Emission 30000 Lux @1m (RGBWA+V max)

Beam Angle 40°

Specifications

Light source 18 x 18W RGBWA+V 6in1 LED

Beam angle 40°

Lux @ 1m Red 3000 Lux, Green 6000 Lux, Blue 6000 Lux, White 12000 Lux, Amber 3000 Lux, UV 2500 Lux, RGBWA+V 30000 Lux

CRI ≥75

DMX Channel Modes 6CH, 10CH-1, 10CH-2

Cooling System Convection (No Fan)

Power Supply Type Switching (internal)

Mains 100-240V - 50/60Hz

Consumption 320W

Light Size (LxHxD) 260x310x250 mm - 10.24x12.21x9.84 in (bracket installed)

Light Weight 4 kg - 8.82 lbs.

Packing Size (LxHxD) 290x290x340 mm - 11.42x11.42x13.38 in

Packing Weight 4.5 kg - 9.92 lbs.