

LIGHTBLASTER 1200WP

1200W 5-Zone Waterproof RGBW LED Strobe & Wash Light

LIGHTBLASTER 1200WP is a LED strobe light designed for outdoor applications where, in addition to power and safety, also versatility is important.

The light source is based on 1200 RGBW 4in1 high brightness LEDs. The emission surface is split into 5 independent zones. It is possible to control the individual colors of each zone via DMX, or to simplify the number of channels in cases of use as a simple strobe or wash fixture.

The die-cast aluminum housing is waterproof, and assures IP65 degree of protection for outdoor use. The LIGHTBLASTER 1200WP is noiseless, thanks to the convection cooling system. It is specifically designed for both indoor and outdoor silent environments, like theatres or live stages with classical/jazz music. The adjustable bracket allows the use with truss. Waterproof Input and Output connections ensure maximum safety in any environment.



PRODUCT DETAILS

Key features

1200 pcs 1W High-Brightness RGBW 4in1 LED

110° Beam Angle

5 Independent Zones

Strobe 0-30Hz

Dimmer 4 Dimmers Curves

5 built-in strobe effects, Static Color Mixing, Auto Control with Fixed Background

DMX512/Manual/Master-Slave/Sound Control Modes

Selectable 18 and 7 DMX Channel Modes

Built-in Auto Programs and Preset Colors for easy use, even without DMX controller

Convection Cooling System, without Fan (completely Noiseless)

Outdoor Use with Waterproof Power In/Out and DMX In/Out Connections

Easy-to-use Front Panel with 4-digit Led Display

Flicker-Free Operation

Specifications

Led source	1200x1W (RGBW 4in1)
Voltage	AC110V-240V
Frequency	50/60Hz
Power Consumption	500W
DMX Channel Modes	7/18CH (switchable)
Control Modes	DMX512/Auto/Master-Slave/Sound Active
Cooling System	No Fan - Convection Cooling
Noise	Noiseless (no fan)
Display	LED Display
DMX Connections	IP65 3-pin In/Out - D17mm
Power Connections	IP65 3-pin In/Out - D35mm
IP Grade	IP65
Fixture Size (WxDxH)	600 x 230 x 100 mm
Fixture Weight	11 kg
Carton Size (WxDxH)	680 x 325 x 200 mm
Carton Weight	12 kg