

## MOODLINER 1430WP

### 14x30W RGBW 4in1 Waterproof Led Bar Washer

Centolight MOODLINER 1430WP is an Outdoor Wash Led Bar with a 25° beam angle. The light source consists of 14pcs of 30W 4in1 Led with RGBW color mixing. The DMX control (with RDM) allows you to control every single color of each LED independently, allowing extremely rich polychromatic effects. The MOODLINER 1430WP is designed for outdoor architectural applications or in all those situations where color wash effect as well as totally silent operation are required (theaters, houses of worship, museums, auditoriums, etc.). The fixture structure is very stout and completely waterproof. The housing is made of die-cast aluminum and steel parts, with high-quality rubber gaskets for maximum isolation and resistance to time. PowerCon In/Out Power connections and DMX In/Out connections with XLR are totally waterproof.



## PRODUCT DETAILS

### Key features

Waterproof Washer Bar with 25° Beam Angle

14x30W RGBW 4in1 LED with over 50,000h lifetime

|                      |                              |
|----------------------|------------------------------|
| <b>Luminous Flux</b> | (RGBW) 3082lux/3m, 794lux/7m |
|----------------------|------------------------------|

|            |       |
|------------|-------|
| <b>CRI</b> | Ra≥85 |
|------------|-------|

Flicker Free Operation

Smooth 16-bit Dimmer

Silent Operation

IP65 Protection Degree

Waterproof DMX and Power connections

## Specifications

|                                 |  |
|---------------------------------|--|
| <b>Light Source</b>             | 14x30W RGBW 4in1 LED   |
| <b>Chip Life</b>                | over 50,000h   |
| <b>Luminous Flux</b>            | (R) 573lux/3m, 152lux/7m; (G) 878lux/3m, 209lux/7m; (B) 886lux/3m, 217lux/7m; (W) 1078lux/3m, 295lux/7m; (RGBW) 3082lux/3m, 794lux/7m; |
| <b>CRI</b>                      | Ra≥85  |
| <b>Refresh Rate</b>             | over 4.000Hz (Flicker-Free)  |
| <b>Beam Angle</b>               | 25°  |
| <b>Dimmer</b>                   | 16-Bit Smooth Linear Dimming   |
| <b>Strobe effect</b>            |  |
| <b>Cooling System</b>           | Convection (without fan)   |
| <b>DMX Channel Modes</b>        | 9/23/56/65 Channels (RDM Included)   |
| <b>Control Modes</b>            | DMX, Master-Slave, Sound, Auto Run, Manual Dimming   |
| <b>Control Panel</b>            | 4 Buttons and LED Display  |
| <b>IP rate</b>                  | IP65   |
| <b>Housing</b>                  | Aluminum + Steel   |
| <b>DMX In/Out</b>               | Waterproof 3-pin XLR   |
| <b>Power Socket</b>             | Waterproof Powercon In/Out   |
| <b>Voltage:100~240V 50/60Hz</b> |  |
| <b>Max Power Consumption</b>    | 450W   |
| <b>Working Temperature</b>      | -30÷55°C   |
| <b>Fixture Size (WxDxH)</b>     | 1012x139x138,5 mm max. - 39.84x5.47x5.45 in (feet included)  |
| <b>Net Weight</b>               | 7,2 kg - 15.87 lbs.  |
| <b>Packing Size (WxDxH)</b>     | 1040x170x220mm - 40.94x6.69x8.66 in  |
| <b>Packing Weight</b>           | 8,3 kg - 18.3 lbs.   |