



XPG Hunter DDR4 Memory Module U-DIMM

# HUNTER BRIGHTENS YOUR GAME



## XPG Hunter DDR4 U-DIMM Memory

Built for dedicated PC enthusiasts and gamers, ADATA XPG Flame DDR4 memory modules deliver all DDR4 benefits with remarkable performance and efficiency. They consume 20% less power than DDR3 while achieving much higher clock speeds, support Intel XMP 2.0, and utilize advanced cooling technologies. XPG Flame DDR4 memory modules therefore overclock easily while maintaining great stability, making them ideal for performance seekers – gaming to competitive benchmarking.

### Features

- Fast speeds up to 3200MHz
- High Capacities up to 32GB
- Superior power efficiency: 20% less draw than DDR3 (operating voltage decreased from 1.5V to 1.2V)
- Supports the latest Intel and AMD platforms
- Intel® XMP 2.0 for accessible overclocking
- RoHS compliant

### Specifications

- Speed: DDR4 2666MHz – 3200MHz
- Module size: 8GB / 16GB / 32GB
- Compatibility: DDR4 2666 CL 19-19-19 at 1.2V
- Operating temperature: 0°C to 85°C
- Storage temperature: -20°C to 65°C
- Operating voltage: 1.2V - 1.35V (1.35V: 3000MHz)
- Dimensions (L x W x H): 133 x 33 x 7.5mm
- Warranty: limited lifetime





## Model Number / EAN Code

Package	Speed/Capacity		Latency	Model Number	EAN Code
Single Tray	2666MHz	8GB	CL 16-18-18	AX4U266638G16-SBHT	4710273775746
		16GB	CL 16-18-18	AX4U2666716G16-SBHT	4710273777610
	3000MHz	8GB	CL 16-20-20	AX4U300038G16A-SBHT	4710273775814
		16GB	CL 16-20-20	AX4U3000716G16A-SBHT	4710273776521
	3200MHz	8GB	CL 16-20-20	AX4U320038G16A-SBHT	4710273778228
		16GB	CL 16-20-20	AX4U3200716G16A-SBHT	4710273778242
		32GB	CL 16-20-20	AX4U3200732G16A-SBHT	4710273777993

## Package Information

### Single Tray

Model	Bulk+HS Weight (g)	Retail Weight (g)	Color Box Dimensions (LxWxH/mm)	Carton Dimensions (LxWxH/mm)	Cuft	Qty per carton	Carton N.W. (g)	Carton G.W. (g)
U-DIMM 8GB	29.7	43.7	170 x 55 x 9	340 x 330 x 212	0.76	200	8,740	10,495
U-DIMM 16GB/32GB	31.7	45.7	170 x 55 x 9	340 x 330 x 212	0.76	200	9,140	10,895