

27" Screen Size

View your applications, spreadsheets and more with a perfect 27 inches screen



IPS Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best




Full HD Resolution

Experience a breathtaking screen clarity that comes with Full HD (1920x1080) resolution



Anti-Flicker Technology

With MSI Anti-Flicker technology, a stable output current for the monitor is provided to protect your eyes




Less Blue Light

Effectively reduce blue light which could cause serious long-term damage to your eyes



Built-in Speakers

Built-in speakers allow you to listen clearly without connecting external speakers



Display Kit Support

Providing the most convenient tool, the proper color & display mode to you while working with it everyday



VESA Mount Support

To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk

Wall Mountable

SPECIFICATIONS

Type / Size	27"
Active Display Area (mm)	597.888(H) x 336.312(V)
Curvature	Flat
Panel Type	IPS
Resolution	1920 x 1080 (Full HD)
Pixel Pitch	0.3114(H) x 0.3114(V)
Aspect Ratio	16:9
Brightness (nits)	250 cd/m ²
Contrast Ratio	1000:1
Refresh Rate	75Hz
Response Time	5ms (GTG)
View Angles	178°(H) / 178°(V)
sRGB	93.1% (CIE 1976)
Surface Treatment	Anti-glare
Display Colors	16.7M
Color Bit	8 bits (6 bits + Hi-FRC)
Video Interface	1x HDMI (1.4) 1x D-Sub (VGA) 1x Mic-in 1x Headphone-out
Speaker	2x 2W
Power Type	Internal Power
Power Input	100~240V, 50~60Hz
Adjustment (Tilt)	-5°~23°
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Dimension (W x D x H)	612.6 x 219.7 x 456.8 mm (24.12 x 8.65 x 17.98 inch)
Weight (NW / GW)	4.2kg (9.26lbs) / 6.2kg (13.67lbs)
Dimension (W x D x H) with Carton	684 x 156 x 448 mm (26.93 x 6.14 x 17.64 inch)
Note	HDMI: 1920 x 1080 (Up to 75Hz) D-Sub: 1920 x 1080 (Up to 60Hz)



1. 1x HDMI (1.4b)
2. 1x D-Sub (VGA)
3. 1x Mic-in
4. 1x Headphone-out
5. Kensington Lock