

PE SCAFFOLDING NETTING / GARDEN NETTING

Product Functions

Used for a variet of applications.

Safety Industry, used to protect public from falling debris on scaffolding, construction sites. Garden Industry, used to protect plants from insects and for decorative purposes.

PROPERTIES	TEST METHOD	VALUE	UNIT	TOLERANCE
PRODUCT THICKNESS	ASTM D6241 : 2014	55.00	GSM	PLUS MINUS 10%
TEARING STRENGTH	DIN 53356	32 N	WARP	PLUS MINUS 10%
TEARING STRENGTH	DIN 53356	17.5 N	WEFT	PLUS MINUS 5%
TENSILE STRENGTH	DIN 53354	358.5 N/5 cm	WARP	PLUS MINUS 5%
TENSILE STRENGTH	DIN 53354	58.6 N/5 cm	WEFT	PLUS MINUS 5%
AIR PERMEABILITY	ASTM 0 737:2004	660.40	CFM	PLUS MINUS 5%
COLOURS		Black, Green		

The information contained in this document is based on testing at an external manufacturers laboratory and is based on mean values. This data sheet is to the best of our knowledge accurate, it shall not however be held constitute or imply any warranty undertaking from Bestport (Europe) Ltd. No liability can be accepted by Bestport (Europe) Ltd in regard to the transporting, distribution or manufacturing of the product. The mentioned characteristics are not vaild if the product has been in contact with harmful chemicals, copper sulphates and if the product is not correctly installed.

Product must be used in strict accordance with our installation instructions

Technical Data Sheet 2016 Version 3