

SPECIFICATIONS

Model Name	PRO B660M-G DDR4
CPU Support	Supports 12 th Gen Intel® Core™ Processors, Pentium® Gold and Celeron® Processors
CPU Socket	LGA 1700
Chipset	Intel® B660 Chipset
Graphics Interface	1x PCIe 4.0 x16 slot
Display Interface	Support 4K@60Hz as specified in HDMI 2.1, DisplayPort 1.4, VGA - Requires Processor Graphics
Memory Support	2 DIMMs, Dual Channel DDR4-4600+MHz(OC)
Expansion Slots	1x PCIe 3.0 x1 slot
Storage	2x M.2 Gen4 x4 64Gbps slots, supports Intel® Optane™ Technology 4x SATA 6Gbps ports
USB Ports	6x USB 3.2 Gen 1 5Gbps (6 Type-A), 6x USB 2.0
LAN	Realtek® RTL8125BG 2.5G LAN
Audio	8-Channel (7.1) HD Audio with Audio Boost

FEATURES



Optimum Thermal Solution

Wavy Fin Design, Direct Touch Cross Heat-pipe, MOSFET Baseplate, double-sided M.2 Shield Frozr, and Frozr AI software ensure the extreme performance with low temp.



Lightning Gen4 Solution

The latest Gen4 PCI-E and M.2 solution with up to 64GB/s bandwidth for maximum transfer speed.



2.5G Network Solution

Featuring premium 2.5G LAN to deliver better network experience.



M.2 Shield FROZR

Strengthened built-in M.2 thermal solution. Keeps M.2 SSDs safe while preventing throttling, making them run faster.



Memory Boost

Advanced technology to deliver pure data signals for the best performance, stability and compatibility.



Core Boost

With premium layout and fully digital power design to support more cores and provide better performance.



EZ Debug LED

Easiest way to troubleshoot.



Frozr AI Cooling


Detect CPU & GPU temperatures and automatically adjust system fan duty to a proper value.



Audio Boost

Reward your ears with studio grade sound quality for the most immersive audio experience.

CONNECTIONS



- | | |
|-------------|-------------------------------|
| 1. VGA | 2. Keyboard / Mouse |
| 3. LAN port | 4. Audio connector |
| 5. HDMI | 6. DisplayPort |
| 7. USB 2.0 | 8. USB 3.2 Gen 1 5Gbps Type-A |