



PHOTOCELLS



Suitable for integration into luminaires or stand alone, our photocells all include a delay circuit to prevent nuisance switching.

Features

- Designed for use with LED loads
- All include a switching delay to prevent false switching due to headlights or cloud cover
- Provide automatic control dusk to dawn
- Deliver increased energy savings

Specification

Material:	Polycarbonate
Colour Finish:	Black / White
IP Rating	IP65*
Guarantee:	1 Year



PC10A



PC15



PC25

Product Code	Description	Max LED Load	Amp	Dimensions	Weight (Kg)	Barcode
PC10A	Photocell Kit	1000W	10A	L: 130 x Ø: 80mm	0.24	5055807609371
PC10AH	Photocell Head	1000W	10A	L: 64 x Ø: 80mm	0.11	5055807609388
PC15	Mini Photocell	1000W	1.5VA	L: 53 x Ø: 16 x W: 29 x D: 43mm	0.04	5055807609395
PC25	Electronic Remote Photocell	400W	5A	L: 53 x W: 45 x D: 30mm x H: 19 x Ø: 20mm	0.07	5055807609401



www.redarrowelectrical.co.uk