

## Be Your Window To The World



Picture and logos

### SELLING POINTS

- 1500R curvature brings the most immersive viewing experience for your work & amusement.
- TÜV certified display protects your eyesight and keeps your eyes healthy
- Anti-Flicker and Less Blue Light technologies prevent your eyes from strain & fatigue
- Ergonomic software, Display Kit, provides the most convenient tool, the proper color & display mode to you while working with it everyday
- 75 Hz refresh rate provides a better viewing experience
- Keep the flexibility for your different devices with multiple input sources: DisplayPort & HDMI
- Standard VESA mountable design
- Always allow you to join an online conference call with built-in speakers



1. 1x DisplayPort (1.2a)
2. 1x HDMI (1.4b)
3. 1x Headphone-out
4. 1x Kensington Lock
5. 5x OSD Button

**SPECIFICATION**

Barcode Info	EAN	4719072977061
	UPC	824142294475
	UCC14	10824142294472
Model	Part No	9S6-3PA8CT-020
	MKT Name	PRO MP271CA
	MKT Spec	PRO MP271CA
	Color	ID1/Black-Black
Display	Screen Size	27" (69 cm)
	Active Display Area (mm)	597.888(H) x 336.312(V)
	Curvature	Curve 1500R
	Panel Type	VA
	Resolution	1920x1080 (FHD)
	Aspect Ratio	16:9
	Dynamic Refresh Rate technology	FreeSync
	HDR (High dynamic range)	N/A
	SDR Brightness (nits)	250
	Contrast Ratio	4000:1
	DCR (Dynamic Contrast Ratio)	100000000:1
	Signal Frequency	30~112 KHz(H) / 48~75 Hz(V)
	Refresh Rate	75Hz
	Response Time (MPRT)	1ms(MPRT)
	Response Time (Tr + Tf)	N/A
	View Angles	178°(H)/178°(V)
	Surface Treatment	Anti-glare
	NTSC (CIE1976 area percentage/overlap)	85.2%/80.9%
	NTSC (CIE1931 area percentage/overlap)	72.4%/71.2%
	sRGB (CIE1976 area percentage/overlap)	97.7%/94.1%
	sRGB (CIE1931 area percentage/overlap)	102.3%/96.6%
	Adobe RGB (CIE1976 area percentage/overlap)	83.7%/82.6%
	Adobe RGB (CIE1931 area percentage/overlap)	75.8%/74.8%
	DCI-P3 (CIE1976 area percentage/overlap)	77.8%/77.7%
	DCI-P3 (CIE1931 area percentage/overlap)	75.4%/75.3%
	Rec.709 (CIE1976 area percentage/overlap)	97.7%/94.1%
	Rec.709 (CIE1931 area percentage/overlap)	102.3%/96.6%
	Rec.2020 (CIE1976 area percentage/overlap)	56.7%/56.7%
	Rec.2020 (CIE1931 area percentage/overlap)	54.1%/54.1%
	Display Colors	16.7M
Color bit	8 bits	
Note_DP	1920 x 1080 (Up to 75Hz)	
Note_HDMI™	1920 x 1080 (Up to 75Hz)	
Note_DVI	N/A	
I/O Ports	HDMI™	1
	HDMI™ version	1.4b
	HDMI™ HDCP version	1.4
	DisplayPort	1
	DisplayPort version	1.2a
	DisplayPort HDCP version	1.3
	Headphone-out	1
	Lock type	Kensington Lock
	Speaker	2
Power	Annual Energy Consumption (KWh)	N/A
	Power Supply Type	Power Cable
	Power Input	100~240V, 50/60Hz
	Adapter's KC safety Number	N/A
	Power Cord Type	C13
	QC Output Power	N/A
PD Output Power	N/A	

In The Box	3.5mm Mic Cable	0
	Switch Case	0
	Portable Screen Protection Case	0
	Monitor Hood	0
	Speaker (Accessories)	0
	DisplayPort Cable	0
	HDMI™ Cable	1
	DVI Cable	0
	USB Type A to Type B Cable	0
	USB Type C to Type A Cable	0
	USB Type C to Type C Cable	0
	Thunderbolt Cable	0
	VGA Cable	0
	3.5mm audio Cable	0
	3.5mm combo audio Cable	0
	Mouse Bungee Unit	0
	VESA Screw	0
	Power Cord	1
	AC Adaptor	0
	Warranty Card	0
Quick Guide	1	
Design	Adjustment (Tilt)	-3.5° ~ 21.5°
	VESA Mounting	100x100mm
	Frameless Design	Yes
Outer Carton Dimension (WxDxH)	Outer Carton Dimension (WxDxH) (mm)	699 x 173 x 499
	Outer Carton Dimension (WxDxH) (inch)	27.52 x 6.81 x 19.65
Product Dimension with Stand (WxDxH)	Product Dimension with Stand (WxDxH) (mm)	610.34 x 237 x 454.8
	Product Dimension with Stand (WxDxH) (inch)	24.03 x 9.33 x 17.91
Product Dimension without Stand (WxDxH)	Product Dimension without Stand (WxDxH) (mm)	610.34 x 79.65 x 367.34
	Product Dimension without Stand (WxDxH) (inch)	24.03 x 3.14 x 14.46
Stand Dimension (WxDxH)	Stand Dimension (WxDxH) (mm)	240 x 237 x 146.6
	Stand Dimension (WxDxH) (inch)	9.45 x 9.33 x 5.77
Dimension & Weight	Inside Carton Dimensions (WxDxH) (mm)	684 x 156 x 474
	Inside Carton Dimensions (WxDxH) (inch)	26.93 x 6.14 x 18.66
	Weight (Net kg)	5.4
	Weight (Gross kg)	7.3
Weight	Weight Without Stand (kg)	4.31
Warranty	Warranty	24M