



DMM Stereo Digital Message Manager

- Stereo MP3, near CD quality
- Trigger Input: 8
- Relay Output: up to 8
- Serial Port: 1 (RS-232/RS-485)
- Input Voltage: 12 - 30 VDC
- Output Power: 15W x 2

The DMM is a rugged industrial MP3 player designed for the most demanding jobs.

Audio programming for the unit is as simple as copying sound files to the memory card via a card reader attached to a computer.

The DMM features a high efficiency low heat class D power amplifier with thermal and short circuit protection (automatic recovery).

A line level output is also available for feeding an external amplifier if required.

Audio playback can be triggered with a variety of methods such as push buttons, motion/alarm sensors and PLCs, in different modes such as:

- Start the playback when the trigger is applied or removed.
- Allow the playback to be interruptible by another trigger or not.
- Play the sound just once or loop till the trigger is removed.

Housed in a compact yet rugged metal case, the DMM can be easily secured into place with the integrated mounting tabs on each side of the unit. Wiring is done via screw terminals and requires only a small screwdriver. The screw terminals are unpluggable, making it fool-proof to replace the unit in the field when necessary.

Audio Design Services Ltd.

St David's House, Adcroft Street, Higher Hillgate, Stockport, SK1 3HW, UK

Tel: +44 (0)161 666 6363

Fax: +44 (0)161 666 6366

Email: info@ads-worldwide.net

Web: www.ads-worldwide.net