

HDMA-350D PLAY

2U 350W 2-Zone Mixer Amplifier with DAB+/FM/USB/BT

Helvia HSMA / HDMA / HMMA Play Series bring a wide offer of integrated PA Sound Reinforcement solutions with digital amplifiers in class-D with processing, zone number from 1 to 4 with 100V outputs, rated powers between 120W and 350W total*, an overall 4-16 Ω power output and a whole series of features such as DAB+receiver, BT audio streaming, USB player, FM radio, mixer with 1 front Mic input with priority, 3 Mic/Line inputs, +48V Phantom Power, 2 stereo Aux Inputs, Level Attenuators for each zone, EMC input at 100V, auxiliary power supply at +24V DC (only models at 120W and 240W). In short, these new mixer-amplifiers enclose in 2 standard 19" units (rack-ear kit included) everything required for a simple and efficient small-to-medium multi-zone installation.



PRODUCT DETAILS

Key features

2-Zone Operation with Output Attenuator

Class-D Power Amplifiers with 350W RMS power

100V Constant Voltage Zone Outputs

4-16 Ω Overall Low-Impedance Output (not controlled by zone attenuators)

Built-in High-Efficiency Digital Audio Processing

Advanced Over Current and Overload Protection

DC 24V Auxiliary Power Supply for Emergency Purposes

EMC 100V Emergency Input with Priority

Multimedia Player with OLED Screen and Remote Control

FM, DAB+, BT 5.0, USB Operation

Mixer with Independent Volume Control, Master Level and 2-Band EQ

3 Mic/Line Balanced Inputs with +48V Phantom

1 Front Mic Unbalanced Input with Priority

2 Stereo Line Auxiliary Inputs

Specifications

2 zones

Rated power	350W
Freq. response	100Hz~16KHz
Power Outputs	100V for each zone; Overall @ 4-16Ω
THD	≤1%
S/N Ratio	≥80dB
N. Channels	4 Mic Inputs, 2x Aux Line Inputs, 1x FM/DAB+/BT/USB Built-In Player
EQ Controls	Low (± 6dB @ 150Hz) High (± 6dB @ 10kHz)
AUX Output	1000mV
AUX 1-2 Inputs	300mV
MIC 1 Input	15mV ±3mV
MIC/Line 2/3/4 Inputs	30mV ±3mV (Mic Position); 300mV (Line Position)
EMC input	100V
BT	5.0 Version with EDR (10m receiving range, without obstacles)
DAB+	170MHz-240MHz
FM Tuner	88MHz-108MHz
USB Audio Format	MP3, WAV, WMA, SBC (FAT32, max. 128GByte)
Main Power	AC220-240V, 50Hz/60Hz
Off-Load Consumption	8W
Full-load Consumption	420W
Auxiliary Power	DC 24V - 10A max.
Fuse	F6AL
Fan Noise Level	38 dB (A-weighted)
Unit Size (WxDxH)	482 x 300 x 88 mm (16.8 x 3.5 x 11.8 in)
Unit Weight	7,45 kg (16.4 lbs.)
Packing Size (WxDxH)	747 x 397 x 164 mm (29.4 x 15.6 x 6.4 in)
Packing Weight	8,95 kg (19.7 lbs.)