

ZEPHIRO FOG 3000

3000 Watt Fog Machine with DMX, wired and wireless control

It is well known how the world of show business and entertainment is based on the fusion of music, images, lights and environmental effects. The sensory involvement of those who enjoy the entertainment event is increasingly present nowadays. Centolight knows very well this need and thanks to the the Zephiro line it offers a wide range of machines for smoke, fog, bubbles, snow and more.

Zephiro Fog 3000 is a powerful and compact fog machine; designed for professional medium-sized on-stage applications and equipped with DMX control, as well as wired and wireless control.

It can generate a persistent and homogeneous fog that greatly enhances visual effects and light beams of any type of fixtures in settings such as theaters, photo and TV studios, film sets, discos, live events, etc.

It has a power output of 3000W and is designed for indoor applications with an output of 710m³/minute. Consumption is about 2L/hour (depending on liquid density). The internal tank is 10 liters.



PRODUCT DETAILS

Key features

710m³/Minute smoke output fills up a medium sized room quickly

Continuous smoke output after a minimal warm-up time

10L Tank capacity for about 5-hour continuous use

One Selectable DMX Channel to control smoke volume emission

Wired Controller to manage Timer, Duration Fog Emission and Volume Fog Emission

Remote controller to start and stop the smoke emission

Specifications

Heating Element	3000 Watt
Output distance	8-10 meters
Warm-up time	Approximately 4 Minutes
Tank capacity	10 Liters
Fog output	710m ³ /Min
Fuel Consumption	about 2L/hour (depending on liquid density)
Ready-indicator inside tank	Yes (Dual color LED)
Wireless remote controller included	Yes - 433,92 MHz (Max 10 Meters)
Wired remote controller included	(Timer, Manual smoke, Continuous fog)
DMX Control	1-CH
Mounting bracket	Included
Power requirements	220V AC, 50Hz
Internal fuse	10A 250V fast blow 20mm glass
Dimensions	703 x 300 x 250 mm (27.7 x 11.8 x 9.8 in)
Weight	10,6 Kg - 23.4 lbs.
Packing Size	760 x 285 x 375 mm (29.9 x 11.2 x 14.8 in)
Packing Weight	12 kg - 26.4 lbs.