

Panther 10 - 10W IP66 Rectangular Horn
Panther 15 - 15W IP66 Rectangular Horn
Panther 30 - 30W IP66 Rectangular Horn



An economically priced, IP66 rated, rectangular ABS horn loudspeaker. Tappable 100V line. Supplied with swivel bracket.

Connections : Black - Common / White - 100V / Green - Earth

Technical Specification

Power Taps 10, 5, 3, 1W
Frequency Response 315Hz - 12.5kHz
Sensitivity 105dB(A) at 1W/1m
Colour Cream
Dimensions H126 x W176 x D185 mm
Weight

Product Code : 04-0001-B10

Technical Specification

Power Taps 15, 10, 5, 3, 1W
Frequency Response 280Hz - 12.5kHz
Sensitivity 108dB(A) at 1W/1m
Colour Cream
Dimensions H162 x W222 x D227 mm
Weight

Product Code : 04-0002-B10

Technical Specification

Power Taps 30, 15, 10, 5, 3, 1W
Frequency Response 250Hz - 16kHz
Sensitivity 109dB(A) at 1W/1m
Colour Cream
Dimensions H209 x W289 x D263 mm
Weight

Product Code : 04-0003-B10