

DISCOVERY 1500



Tool Specifications

- Charge Methods: Household Outlet Charge (adapter charging)
- Car Outlet Charge Solar Panel Charge
- Household Outlet Charge Time: 5h (300W max)
- Car Outlet Charge Time: 25.2h (12V 60W max)
- Solar Panel Charge Time: 2.5h (12-28V 600W)
- Battery Type: 18650 cell: 18650 Lithium Battery
- 1328Wh (21.6V/59.8Ah)
- 5.0Ah, 3.6V
- 6S23P
- Continuous Watts: 1500W
- Surge Watts: 3000W
- Wave Type: Pure Sine
- Frequency: 50Hz
- AC Voltage: 230V
- DC Voltage: 12V 10A
- Voltage: 230V

- AC Output: 1500w*1
- USB-A Output (quick charging): 2X, 18W, max 36W
- Type C Output: 2x, 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3A, max 60W
- Cigarette Output: 12V 10A *1
- LED Light
- 10W Wireless Charger *1
- Display Features: % Battery indication
- Remaining working time
- Remaining time to fully charge
- Output/Input Watts
- Higher/Lower Temperature Warning
- Low Battery Warning

Protections

- Overload Protection
- Voltage Control
- Over Current Protection
- Short Circuit Protection
- Temperature Control
- Over Charging Protection
- Low Battery Alarm