

# Galaxy 1000 and 2000

Compact, Lightweight and Portable Work Lights

Rechargeable Work Lights



Fold flat for easy storage



- |               |           |
|---------------|-----------|
| 1000lm        | 2000lm    |
| 10m Beam      | 20m Beam  |
| 1.4 to 3.2hrs | 2 to 4hrs |
| IP54          | IP54      |

- High impact ABS housing
- Shatterproof polycarbonate lens
- Carry handle and floor stand
- Rechargeable lithium battery
- Overcharge and discharge protection
- Battery charging indicator
- Lightweight under 730g
- Ideal for DIY, inspection work and construction sites

2 models available:

	Galaxy 1000	Galaxy 2000
	1000 Lumens	2000 Lumens
	Up to 10m beam	Up to 20m beam
	1.4 to 3.2hrs runtime	2 to 4hrs runtime
MODE	High   Low	High   Low
	Li-ion 3.7V 4000mAh, 15Wh	7.4V 4000mAh, 30Wh, Li-ion
	3.5hrs charging time	6.5hrs charging time
	IP54	IP54
	72 x 76 x 49.5mm	72 x 76 x 49.5mm
	539g	730g
CODE	NSGALAXY1000	NSGALAXY2000

360° handle and stand



Supplied with GALAXY1000: USB charging cable  
Galaxy 2000: USB-DC1 charging cable

**Optional Accessories:**  
UK or EU adaptor: CH-USB-UK/EU  
12/24V Vehicle charger: CHIC3.7-LI-ION  
Tripods: 2m tripod: SPTRIPODSS2M



Tripod mountable  
check optional  
accessories  
for more details

**YouTube**  
Scan for multi-language information

