

NOKIA



105 2G D.Sim - Charcoal

DATA SHEET

Product Information

EAN	6438409086037
Brand	Nokia
SKU	10385524
Manu Part #	1GF019CPA2L05

Weight & dimensions

Depth	14.4 mm
Volume	82.14 cm ³
Height	115.1 mm
Width	49.4 mm
Weight	78.7 g

Technical details

Doesn't contain	Nickel, PVC
Sustainability compliance	Y
International Protection (IP) code	IP52
Introduction year	2023
Battery weight	21.4 g
Type	Feature phone
Subscription type	No subscription
Housing material	Polycarbonate (PC)
Operating system installed	Series 30+
Product colour	Charcoal
Sustainability certificates	REACH, RoHS
Built-in flashlight	Y

Protection features	Dust resistant, Splash proof
Package volume	464.26 cm ³

Phone features

Form factor	Bar
Personal info management (PIM)	Alarm clock, Calculator, Calendar

Packaging data

Package depth	124 mm
Package width	117 mm
Package height	32 mm
Package weight	136 g

Network

2G bands (primary SIM)	900,1800 MHz
SIM card capability	Dual SIM
SIM card type	MiniSIM
Mobile network generation	2G
Wi-Fi	N

Data network	GSM
--------------	-----

GPS Performance

Assisted GPS (A-GPS)	N
Position location	N

Messaging

Short Message Service (SMS)	Y
-----------------------------	---

Data transmission

Bluetooth	N
-----------	---

Power

Standby time (2G)	528 h
Talk time (2G)	12 h
Battery capacity	1000 mAh

Ports & interfaces

USB port	Y
----------	---

Headphone connectivity	3.5 mm
USB version	1.1
USB connector type	Micro-USB

Packaging content

User guide	Y
Cables included	Micro-USB

Audio

FM radio	Y
Speakers	Mono

Display

Touchscreen	N
External display	N
Display diagonal	4.57 cm (1.8")
Display resolution	160 x 120 pixels

Memory

--	--

Flash card support	N
Compatible memory cards	Not supported

Logistics data

Country of origin	Vietnam
-------------------	---------

Camera

Front camera	N
Rear camera	N

Product Description

Quality that keeps you connected Trust goes a long way. Nokia 105 boasts the kind of build quality for which Nokia phones are known, proven by rigorous product testing. With a 25% bigger battery than its predecessor, Nokia 105 is a phone you can rely on – day in, day out. Quality build Backed by rigorous product testing to ensure it can take life's knocks. Wireless FM radio Tune in to local stations with or without a headset. Long-lasting battery Get up to 12 hours of talk time or 22 days of standby from a single charge. Easy to use Feels intuitive with a large display and tactile keyboard. Local music and news at your fingertips Listen to news on your morning commute or play music at home. The wireless FM radio works with or without a headset, so you're good to go. Bigger battery Nokia 105 features a 25% bigger battery than the previous model, giving you up to 22 days of standby and up to 12 hours of talk time per charge. Top up with a standard Micro USB cable. Keep your contacts close With space for up to 2,000 contacts and 500 SMS messages, there's nothing to stop you staying in touch. As fun as it is useful You never know when a torch will come in handy. Thankfully, Nokia 105 has one built in. And when it's time to relax, kick back with a few games.

