

## CL48PM

### For Indoor/Semi-Outdoor Use

This stylish and powerful evaporative air cooler keeps indoor and semi-outdoor environments comfortably cool and breezy. Its powerful motor and wide fan blades help to deliver strong air flow while the 3-sided honeycomb cooling media keep performance optimal. A continuous water supply connection, large water tank, and built-in water overflow protection system allow long periods of cooling, making it ideal for more demanding applications.



Control Panel



Product Dimensions (in): 24.4 (W) 14.8 (D) 34.8 (H)  
Net Weight: 12.9 kg / 28.4 lbs

## FEATURES & BENEFITS



Low Power Consumption  
140 Watts\*



Large Water Capacity  
40 L\*\*



Cools Up To  
57 m<sup>2</sup> (610 ft<sup>2</sup>)\*



Powerful Air Flow  
1800 m<sup>3</sup>/hr (1062 CFM)\*



3 Speeds:  
High / Medium / Low



Ice Compartment For  
Faster Cooling



Wide Fan Bladed



Mechanical  
Control Panel



3 Sided Honeycomb  
Cooling Media for  
Optimum Cooling



Continuous Water  
Supply Connection

Find out more about evaporative air coolers:  
[www.honeywellhomecomfort.com](http://www.honeywellhomecomfort.com)

\* All specifications mentioned are under test conditions, actual performance depends on ambient conditions. Specifications may vary in different countries and subject to change without prior notice.  
\*\* Water Capacity is the total volume of water that can be contained within the air cooler water tank and water distribution system.

### Scott Brothers Ltd

1 Whiteside Station Road  
Holmes Chapel Cheshire  
CW4 8AA  
UK

Email: [enquiries@scottbrothersltd.co.uk](mailto:enquiries@scottbrothersltd.co.uk)  
Telephone: +44 (0) 1477 539 500

© 2018 JMATEK Limited.  
All rights reserved. The Honeywell  
Trademark is used under license  
from Honeywell International Inc.  
Honeywell International Inc. makes  
no representations or warranties  
with respect to this products  
This product is manufactured by  
JMATEK Limited.

# Honeywell