



DORO CONGRESS - 100 Business Phone

APPLICATIONS

This uniquely designed telephone is ideally suited for any environment.

Boasting standard features such as a headset port and selectable message waiting indicator, this business class telephone is perfect for use in:

- Call centre environments
- Nursing homes/Hospitals
- Offices
- Government Departments
- Hotels/Motels

Built to perform and highly durable, this sleek modern phone is an affordable and reliable alternative for any business.



DORO CONGRESS - 100 Business Phone

FEATURES

- Designer business class telephone
- Headset port with one button operation and LED indicator
- Data port for convenient computer connection and data transfer
- 10 memories for frequently dialled numbers or PABX functions
- Message waiting lamp for voicemail indication
- Visual ring indicator for incoming calls
- Hold key with LED and one touch operation
- Optional ring tone "Off"
- Pause button, # and * can be programmed for PABX functions
- Adjustable 5 position handset volume control
- Hearing aid compatible
- Last number redial
- Three selectable ring melodies
- Selectable recall for specific PABX requirements
- Latching mute function to allow private enquiries
- Adjustable ringer volume (Hi/Med/Lo/Off)
- Extra long flexible handset cord for convenience

Grey - Barcode number: 7319770 586601 - Order Part Number: 58660



Additional Technical Data

Height: 80mm
 Width: 175mm
 Depth: 215mm
 Weight: 654 grams

- Superior immunity to RF interference caused by mobile phones, DECT phones etc.
- Detachable modular handset cord (extending to 2.12 metres)
- Dual injection dial keys
- Selectable message wait settings (80-100v, 12vLR, 48vLR)
- Selectable recall (100/270/600ms)
- Tone/pulse selectable
- Modular line cord terminated with RJ45 plug plus converter plug

The above feature list is not exhaustive. Please consult the relevant product manual for a full list of features. Due to continued product improvement the product's features and specifications may vary slightly from the actual product shown.