

FEATURED



ABM2S-A-C0 Cable Tie Mount, Black, ABS, Rubber Adh., 1x1", PK100

ABM2S-A-C0

Panduit's ABM2S-A-C0 4-way rubber-based adhesive backed cable tie mounts have been designed for fast installation and long-term performance and reliability. They are made of Weather Resistant ABS plastic. These mounts can be used with miniature, intermediate, and standard cable ties and are designed for indoor environments. They are 1" x 1" (25.4mm x 25.4mm), supplied in strips of 2, are black in color and come in packages of 100.

Specifications

Application	Used with Miniature, Intermediate, and Standard Cables Ties
Product Type	Cable Tie Mount
Color	Black
Environment	Indoor
Material	ABS
Maximum Compatible Panel Thickness (In.)	0.04
Maximum Compatible Panel Thickness (mm)	1
Maximum Operating Temperature (°C)	49
Maximum Operating Temperature (°F)	120
Minimum Operating Temperature (°C)	-29
Minimum Operating Temperature (°F)	-20
Mount Method	Adhesive Tape
Mounting Hole Thread Size	0.15
Overall Height (In.)	0.2
Overall Height (mm)	5.1
Overall Length (In.)	1
Overall Length (mm)	25.4
Overall Width (In.)	1
Overall Width (mm)	50.3
Standards Met	CE Compliant, UL Recognized: E136577, RoHS Compliant
Static Load Capacity (kg)	0.227
Static Load Capacity (lb)	0.5
For Use With	Miniature, Intermediate, Standard Cross-Section Ties

Packaging Detail

UPC	07498383899
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0539
Std. Ctn. Qty.	500
Std. Ctn. Volume (cf)	0.2695