

 Product iQ will be unavailable on Saturday, April 13th from 8:00am to 1:00pm CST due to site maintenance. We apologize for any inconvenience.

UL Product iQ[®]



Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

Heaters, Specialty - Component

COMPANY

DBK David + Baader GmbH

Nordring 26

Ruelzheim, Rheinland-Pfalz 76761 Germany

E120970

Marking: Company name and model designation.

Note: For additional marking information, refer to the [Guide Information Page](#).

Model(s): DEB05, DEB06, EB01, EB02, EB03, EB04, EB04CD, EB05, EB05CD, EB06, EB07, EB08, EB09, EB10, EB11, EB12, EB13, EB14, EB15, EB16, EB17, EB18, EB19, EB20, EB21, EB22, EB23, EB24, EB25, EB26, EB27, EB28, EBG 3/24, EBG*, EC04, EC04 Z 1/07, EC04 Z 1/11, EC05, EC05 Z 2/11, EC05 Z 2/16, EC06 Z 3/16, EC06 Z 4/11, EC06 Z 4/18, HP03, HP04, HP05, HP06, HP07, HP08, HP09, HP10, HP11, HP12, HP13, HP14, HP15, HP16, HP17, HP18, HP19, HP20, HP21, HP22, HP23, HP24, HP25, HP26, HP27, HP28, HPG*, HR01*, HR02*, HR03*, HR04*, HR05*, HR06*, HR08*, HR09*, HR11*, HR15*, HR18*, HR20*, HR22*, HR40*, HS05, KOQ45-80084, KOQ45-80085, K4T88-80050, M0E29-60101, Nimbus B, Nimbus D, Nimbus E, Nimbus P, VER 2/20 230V, VER 2/20 400-460V, VER 3/20 230V, VER 3/20 400-460V, VER-E 3/18 100-240V, VER-F 2/18 110-240V, VER-F 2/20 380-480V, VER-N 2/20 380V

Model(s): A-J followed by 001-9999, followed by 01-99, followed by 000-575, followed by 0-15, may be followed by the suffix A

Model(s): EA01, followed by 1 to 6, followed by 04, 05, 23, 27 or 29.

Model(s): HOL followed by 001 to 9999, followed by 0 to 575, followed by 01 to 10, may or may not be followed by A, may be followed by suffix -3000V

Model(s): HT01, HT02 or HT03, followed by 2, 3 or 4, followed by number which determines the reference temperature divided by 10.

HRGR Series, Model(s): HRGR, followed by 02, 03, 04, 05, 06, 07, 08, 09, 10, 11, or 12 12, followed by /, followed by 10, 12, 14, 21 or 22, followed by 73x68

HRK Series, Model(s): HRK01*, HRK02*, HRK03*, HRK04*, HRK05*, HRK06*, HRK08*, HRK09*, HRK11*, HRK15*, HRK18*, HRK20*, HRK22*, HRK40*, HRKK01*, HRKK02*, HRKK03*, HRKK04*, HRKK05*, HRKK06*, HRKK08*, HRKK09*, HRKK11*, HRKK15*, HRKK18*, HRKK20*, HRKK22*, HRKK40*

Series DUV, Model(s): DUV 2/18 100-240V, DUV 3/18 100-240V, DUV 4/18 100-240V, DUV-L 2/18 100-240V, DUV-L 3/18 100-240V, DUV-L 4/18 100-240V

* - Followed by numbers and letters.

Last Updated on 2023-05-23

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."