



Color: ■ silver-colored

#### Technical data

Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	500 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

#### Physical data

Depth	0.09 mm
Marking surface	44 x 99 mm

#### Mechanical data

Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

#### Material data

Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	380 g
Fire load	0 MJ

### Environmental requirements

Ambient temperature (storage)	≤+21 °C
Ambient temperature (operation)	-40 ... +150 °C
Relative humidity	40 ... 50 %

### Commercial data

Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-40-06-29
eCl@ss 9.0	27-40-06-29
ETIM 9.0	EC001288
ETIM 8.0	EC001288
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821632627
Customs tariff number	39199080888

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

### Downloads

#### Environmental Product Compliance


##### Compliance Search

Environmental Product  
Compliance 210-804



### Documentation

#### Operating Instructions

210-804 Information on handling print material	1 28.08.2020	pdf 1347.39 KB	
---	-----------------	-------------------	---

### 1 Compatible Products

#### 1.1 Optional Accessories

##### 1.1.1 Marking

##### 1.1.1.1 Marking device



##### Item No.: 258-5000

Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material