



The DNA of tech.™

Additional Wafer Fab Site Qualification

For further information, please contact your regional Vishay office.

CONTACT INFORMATION

Americas

Vishay Semiconductors
One Greenwich Place
-
Shelton CT United States 06484
Phone: +1 402 563 6866
Fax: +1 402 563 6296
Diodes-Americas@vishay.com

Europe

Vishay Semiconductors
Theresienstrasse 2
-
Heilbronn Germany 74072
Phone: +49 7131 7498 656 (715)
Fax: +49 7131 67 2938
Diodes-Europe@vishay.com

Asia

Vishay Semiconductors
37A Tampines Street 92 #07-01
-
Singapore 528886
Phone: +65 6788 6668
Fax: +65 6788 988
Diodes-Asia@vishay.com

Description of Change: To secure the supply chain for our customers, Vishay Semiconductors announces the qualification of an additional Wafer Fab for some Part Numbers.

Reason for Change: Capacity increase and supply chain security.

Expected Influence on Quality/Reliability/Performance: There will be no effect on product quality, reliability or performance.

Part Numbers/Series/Families Affected: Please see materials list on the succeeding page.

Vishay Brand(S): Vishay Semiconductors

Time Schedule:

Start Shipment Date: Thu Dec 5, 2024

Sample Availability: Samples available upon request

Product Identification: Batch code (contact factory for the details)

Qualification Data: Available upon request

This PCN is considered approved, without further notification, unless we receive specific customer concerns before Wed Dec 4, 2024 or as specified by contract.

Issued By: Fabio Bertuccio, Fabio.Bertuccio@Vishay.com



Product Change Notification



Product Group: DD/Fri Oct 4, 2024/PCN-DD-031-2024-REV-0

The DNA of tech.™

VS-12F100M	VS-12F120M	VS-12F60M	VS-16F120M	VS-I730B
VS-16F80M	VS-25F100M	VS-25F120M	VS-25F10M	VS-25F40M
VS-25F60M	VS-25F80M	VS-6F100M	VS-1N3672A	VS-12F100
VS-12F120	VS-12F10	VS-12F20	VS-12F40	VS-12F60
VS-12F80	VS-1N1199A	VS-1N1200A	VS-1N1201A	VS-1N1202A
VS-1N1203A	VS-1N1204A	VS-1N1205A	VS-1N1206A	VS-1N3670A
VS-1N3671A	VS-16F100	VS-16F120	VS-1N3624	VS-1N3673A
VS-16F10	VS-16F20	VS-16F40	VS-16F60	VS-16F80
VS-80-0443	VS-I900B	VS-S1329	VS-25F100	VS-25F120
VS-S1362	VS-25F10	VS-25F20	VS-25F40	VS-25F60
VS-25F80	VS-I775F	VS-S1360	VS-6F100	VS-6F120
VS-6F10	VS-6F20	VS-6F40	VS-6F60	VS-6F80
VS-12FR100M	VS-12FR120M	VS-12FR60M	VS-6FR20M	VS-16FR120M
VS-I731B	VS-16FR20M	VS-16FR80M	VS-25FR100M	VS-25FR120M
VS-25FR10M	VS-25FR40M	VS-25FR60M	VS-25FR80M	VS-6FR100M
VS-12FR100	VS-12FR120	VS-12FR10	VS-12FR20	VS-12FR40
VS-12FR60	VS-12FR80	VS-1N1199RA	VS-1N1200RA	VS-1N1201RA
VS-1N1202RA	VS-1N1203RA	VS-1N1204RA	VS-1N1206RA	VS-1N3671RA
VS-16FR100	VS-16FR120	VS-1N3624R	VS-1N3673RA	VS-16FR10
VS-16FR20	VS-16FR40	VS-16FR60	VS-16FR80	VS-80-0692
VS-80-1100	VS-I901B	VS-25FR100	VS-25FR120	VS-25FR10
VS-25FR20	VS-25FR40	VS-25FR60	VS-25FR80	VS-I776F
VS-S1361	VS-6FR100	VS-6FR120	VS-6FR10	VS-6FR20
VS-6FR40	VS-6FR60	VS-6FR80	VS-40HF100M	VS-40HF120M
VS-40HF10M	VS-40HF20M	VS-40HF40M	VS-40HF80M	VS-1N3766
VS-1N3767	VS-1N3768	VS-40HF100	VS-40HF120	VS-41HF100
VS-41HF120	VS-42HF100	VS-42HF120	VS-80-5732	VS-80-7252
VS-40HF10	VS-40HF20	VS-41HF10	VS-1N1183	VS-1N1184
VS-1N1185	VS-1N1186	VS-1N1187	VS-1N3208	VS-1N3209
VS-40HF40	VS-41HF20	VS-41HF40	VS-42HF20	VS-42HF40
VS-1N1188	VS-1N1189	VS-1N1190	VS-1N2160	VS-1N3210
VS-1N3211	VS-1N3212	VS-1N3213	VS-1N3214	VS-1N3765
VS-40HF60	VS-40HF80	VS-41HF60	VS-41HF80	VS-42HF60
VS-42HF80	VS-80-5730	VS-80-5731	VS-I603E	VS-I631C
VS-S1327	VS-40HFR100M	VS-40HFR120M	VS-40HFR10M	VS-40HFR20M
VS-40HFR40M	VS-40HFR60M	VS-40HFR80M	VS-41HFR40M	VS-42HFR80M
VS-1N3766R	VS-1N3768R	VS-40HFR100	VS-40HFR120	VS-41HFR100
VS-41HFR120	VS-42HFR100	VS-42HFR120	VS-80-6065	VS-1N1183R
VS-1N1184R	VS-1N1185R	VS-1N1186R	VS-1N1187R	VS-1N1188R
VS-1N1189R	VS-1N1190R	VS-1N3208R	VS-1N3209R	VS-1N3210R
VS-1N3211R	VS-1N3212R	VS-1N3214R	VS-40HFR10	VS-40HFR20
VS-40HFR40	VS-40HFR60	VS-40HFR80	VS-41HFR10	VS-41HFR20
VS-41HFR40	VS-41HFR60	VS-41HFR80	VS-42HFR20	VS-42HFR40
VS-42HFR60	VS-42HFR80	VS-80-6063	VS-80-6064	VS-I604E
VS-I632C	VS-S1328	VS-50PF120	VS-52PF120	VS-50PF40
VS-50PF80	VS-50PFR120	VS-52PFR120	VS-50PFR40	VS-50PFR80
VS-50PFR120W	VS-50PFR40W	VS-50PFR80W	VS-50PF120W	VS-50PF40W
VS-50PF80W	VS-40HF140M	VS-40HF160M	VS-40HF140	VS-41HF140
VS-42HF140	VS-IA85A	VS-40HF160	VS-42HF160	VS-40HFR140M
VS-40HFR160M	VS-41HFR160M	VS-40HFR140	VS-40HFR160	VS-41HFR140
VS-42HFR140	VS-IA86A	VS-42HFR160	VS-50PF140	VS-50PF160
VS-50PFR140	VS-50PFR160	VS-50PFR140W	VS-50PFR160W	VS-50PF140W
VS-50PF160W	VS-82-0509	VS-82-0514	VS-T110HF10	VS-T110HF100
VS-T110HF120	VS-T110HF20	VS-T110HF40	VS-T110HF60	VS-T110HF80
VS-T85HF10	VS-T85HF100	VS-T85HF120	VS-T85HF20	VS-T85HF40
VS-T85HF60	VS-T85HF80			

Industrial PN only. No ZVEI and PPAP needed.