

SIMATIC S7-1200, Digital output SB 1222, 4 DQ, 24 V DC 200 kHz



Figure similar

General information	
Product type designation	SB 1222, DQ 4x24 V DC 200 kHz
Input current	
from backplane bus 5 V DC, typ.	35 mA
Power loss	
Power loss, typ.	0.5 W
Digital outputs	
Number of digital outputs	4; MOSFET, solid-state (current-sinking/current-sourcing)
• in groups of	4
Short-circuit protection	No
Switching capacity of the outputs	
• with resistive load, max.	0.1 A
Load resistance range	
• upper limit	11 Ω
Output voltage	
• Rated value (DC)	24 V
• for signal "0", max.	1 V; with 10 kOhm load
• for signal "1", min.	L+ (-1.5 V)
Output current	
• for signal "1" permissible range, max.	0.1 A
Cable length	
• shielded, max.	50 m
Interrupts/diagnostics/status information	
Diagnostics indication LED	
• for status of the outputs	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	Yes
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	-20 °C

• max.	60 °C
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Air pressure acc. to IEC 60068-2-13</b>	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
<b>Relative humidity</b>	
• Operation at 25 °C without condensation, max.	95 %
<b>Mechanics/material</b>	
Enclosure material (front)	
• Plastic	Yes
<b>Dimensions</b>	
Width	38 mm
Height	62 mm
Depth	21 mm
<b>Weights</b>	
Weight, approx.	35 g

**last modified:** 3/12/2024 