

Product datasheet

Specifications



wall-mounting enclosure polyester monobloc IP66 H430xW330xD200mm glazed door

Local distributor code:
403422654

NSYPLM43TG

EAN Code: 3606480776540

Main

| | |
|--------------------|----------------------------|
| Range | Thalassa |
| Product name | Thalassa PLM |
| Device short name | PLM |
| Enclosure type | Multi-purpose |
| Category | Compact enclosure |
| Nominal height | 430 mm |
| Nominal width | 330 mm |
| Nominal depth | 200 mm |
| enclosure mounting | Wall mounted |
| Device composition | 1 body 1 door 2 lock |
| Door type | Transparent |
| Lock type | 3 mm double-bar lock |

Complementary

| | |
|-----------------------------|--|
| Number of locks | 2 |
| Mounting plate description | Without mounting plate |
| Accessibility for operation | Front |
| Removable parts | Door by hinges |
| Material | Body: polyester reinforced with fibreglass Door: tempered glass |
| Colour | Grey (RAL 7035) |
| Standards | NEMA classification 13 IEC 62208 NEMA classification 4X |
| Product certifications | UL |
| Electrical insulation class | Class II |

Environment

| | |
|-------------------------|--------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK08 conforming to IEC 62262 |
| Fire resistance | 960 °C conforming to IEC 62208 |

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -40...80 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------------|-----|
| Unit Type of Package 1 | PCE |
|------------------------|-----|

| | |
|------------------------------|---|
| Number of Units in Package 1 | 1 |
|------------------------------|---|

| | |
|------------------|-----------|
| Package 1 Height | 25.000 cm |
|------------------|-----------|

| | |
|-----------------|-----------|
| Package 1 Width | 35.000 cm |
|-----------------|-----------|

| | |
|------------------|-----------|
| Package 1 Length | 49.000 cm |
|------------------|-----------|

| | |
|------------------|----------|
| Package 1 Weight | 6.038 kg |
|------------------|----------|

| | |
|------------------------|-----|
| Unit Type of Package 2 | PAM |
|------------------------|-----|

| | |
|------------------------------|----|
| Number of Units in Package 2 | 50 |
|------------------------------|----|

| | |
|------------------|------------|
| Package 2 Height | 191.000 cm |
|------------------|------------|

| | |
|-----------------|------------|
| Package 2 Width | 100.000 cm |
|-----------------|------------|

| | |
|------------------|------------|
| Package 2 Length | 120.000 cm |
|------------------|------------|

| | |
|------------------|------------|
| Package 2 Weight | 315.000 kg |
|------------------|------------|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations

Technical Illustration

Dimensions



Image of product / Alternate images

Alternative



Image of product in real life situation

