

KRYPTON

RECHARGEABLE FLOODLIGHTS

Krypton is a lightweight, portable, rechargeable floodlight with a sleek design. Push button operation features 3 light levels and amber SOS flashing sequence, plus last level memory on/off function.



Features

- Up to 12 hours of light when fully charged
- Choice of 3 light levels - 100%/60%/20%
- Handy amber SOS flashing function
- Fully adjustable stand, folds flat for storage.



Specification

Code	Description	Lumen Output	Emergency Lumen Output	Wattage	Efficacy
KRY20	Krypton Rechargeable Floodlight 20W	1000 / 600 / 200 lm		20W	

Product Information

Warranty	3 Years
Colour Appearance (CCT)	6000K
IP Rating	IP65
IK Rating	IK08
Voltage	3.7V DC Charge
Material (Body/Housing)	Die-Cast Aluminium
Material (Diffuser/Cover)	Polycarbonate

Colour Rendition (CRI)	Ra 80
Colour Finish	Yellow
LED Life Expectancy	L70B50 30,000 Hours
Driver Type	Fixed Output
Approval	UKCA & CE
Working Temperature	-20°C to 45°C



KRYPTON

RECHARGEABLE FLOODLIGHTS

Packaging Information

Dimensions (mm)	L: 280 x W: 218 x D: 183 mm
Product Net Weight (kg)	0.87 kg
Barcode	5055807622844
Box Dimensions (mm)	L: 290 x W: 240 x D: 60 mm
Box Gross Weight (kg)	1.0 kg

Units/Outer Carton	10
Outer Carton Barcode	15055807622841
Outer Carton Dimensions (mm)	L: 500 x W: 388 x D: 315 mm
Outer Carton Gross Weight (kg)	10.75 kg

