



Part Number : [150612605](#)

Product Description : 1.00mm Pitch Premo-Flex Round Flat Cable (RFC) Jumpers, Round-to-Flat (Type B), 152.00mm Cable Length, Tin (Sn) Plating, 5 Circuits

Series Number : 15061

Status : Active

Product Category : Flexible Printed Circuit (FPC) Flex Jumpers



---

## Documents & Resources


### Drawings

[150612605\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Flexible Printed Circuit (FPC) Flex Jumpers
Series	15061
Description	1.00mm Pitch Premo-Flex Round Flat Cable (RFC) Jumpers, Round-to-Flat (Type B), 152.00mm Cable Length, Tin (Sn) Plating, 5 Circuits
Comments	Round-to-Flat, Type B
Product Name	Premo-Flex RFC Jumper
UPC	196823685101

### Electrical

Current - Maximum per Contact	1.25A
Voltage - Maximum	60V AC

### Physical

Cable Length	152.00mm
Circuits (Loaded)	5
Contact Layout Type	B (round-to-flat)
Design Feature	Direct to Board
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Termination Style	Solder
Wire/Cable Type	Round Flex Cable
Wire Size (AWG)	28