



Part Number : [150612610](#)

Product Description : 1.00mm Pitch Premo-Flex Round Flat Cable (RFC) Jumpers, Round-to-Flat (Type B), 152.00mm Cable Length, Tin (Sn) Plating, 10 Circuits

Series Number : 15061

Status : Active

Product Category : Flexible Printed Circuit (FPC) Flex Jumpers




Documents & Resources

Drawings

[150612610_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)4144-DC (27 June 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Flexible Printed Circuit (FPC) Flex Jumpers |
| Series | 15061 |
| Description | 1.00mm Pitch Premo-Flex Round Flat Cable (RFC) Jumpers, Round-to-Flat (Type B), 152.00mm Cable Length, Tin (Sn) Plating, 10 Circuits |
| Comments | Round-to-Flat, Type B |
| Product Name | Premo-Flex RFC Jumper |
| UPC | 196823685118 |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.25A |
| Voltage - Maximum | 60V AC |

Physical

| | |
|-------------------------------|-------------------|
| Cable Length | 152.00mm |
| Circuits (Loaded) | 10 |
| Contact Layout Type | B (round-to-flat) |
| Design Feature | Direct to Board |
| Material - Plating Mating | Tin |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.00mm |
| Temperature Range - Operating | -40° to +105°C |
| Termination Style | Solder |
| Wire/Cable Type | Round Flex Cable |
| Wire Size (AWG) | 28 |