

## ix Type A OM Profinet B PVC 3.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 313 1409 030
Specification	ix Type A OM Profinet B PVC 3.0m
HARTING eCatalogue	<a href="https://b2b.harting.com/33483131409030">https://b2b.harting.com/33483131409030</a>

### Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® PushPull IP20 Type A Overmoulded IDC termination
Connector 2	HARTING ix Industrial® PushPull IP20 Type A Overmoulded IDC termination
Type of cable	Copper cable (round)

### Version

Cable length	3 m
Number of cores	4
Core structure	4x AWG 22/7
Number of contacts	10

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s



**Pushing Performance**  
Since 1945

## Technical characteristics

Limiting temperature	-30 ... +70 °C unmoved
	-20 ... +60 °C moved

## Material properties

Material (cable)	PVC
Colour (cable)	Green

## Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
	UN/ECE-R 118 fire protection for rolling stock
PROFINET	Yes

## Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140330337
eCl@ss	27061801 Data and communication cable (copper)