

ix Type B OM 5x2xAWG26 PVC 3.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 323 2A32 030
Specification	ix Type B OM 5x2xAWG26 PVC 3.0m
HARTING eCatalogue	https://b2b.harting.com/33483232A32030

Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® PushPull IP20 Type B Overmoulded IDC termination
Connector 2	HARTING ix Industrial® PushPull IP20 Type B Overmoulded IDC termination
Type of cable	Copper cable (round)

Version

Cable length	3 m
Number of cores	10
Core structure	5x 2x AWG 26
Number of contacts	10

Technical characteristics

Rated current	1.5 A
Rated voltage	50 V AC 60 V DC



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +80 °C unmoved -5 ... +70 °C moved
----------------------	---

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy IEC 61076-3-124
----------------	---

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140333437
eCl@ss	27060311 Assembled sensor actuator-line