

EMI-Common Mode Choke



Automotive for Signal Line

AWU000CMC-KIT JIS 2012, 3216, 3325, 4532 Size

Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Impedance(Ω)	RDC(Ω) Max.	IDC(mA)	Rated Voltage(Vdc)	Quantity
AWCU00201212300M02	2.0	1.2	1.2	2012/0805	30	0.2	450	50	20
AWCU00201212670M02	2.0	1.2	1.2	2012/0805	67	0.25	400	50	20
AWCU00201212750M02	2.0	1.2	1.2	2012/0805	75	0.3	360	50	20
AWCU00201212900M02	2.0	1.2	1.2	2012/0805	90	0.35	330	50	20
AWCU00201212121M02	2.0	1.2	1.2	2012/0805	120	0.3	400	50	20
AWCU00201212161M02	2.0	1.2	1.2	2012/0805	160	0.35	350	50	20
AWCU00201212181M02	2.0	1.2	1.2	2012/0805	180	0.35	330	50	20
AWCU00201212201M02	2.0	1.2	1.2	2012/0805	200	0.35	330	50	20
AWCU00201212221M02	2.0	1.2	1.2	2012/0805	220	0.35	310	50	20
AWCU00201212261M02	2.0	1.2	1.2	2012/0805	260	0.4	300	50	20
AWCU00201212301M02	2.0	1.2	1.2	2012/0805	300	0.4	290	50	20
AWCU00201212361M02	2.0	1.2	1.2	2012/0805	360	0.45	280	50	20
AWCU00201212371M02	2.0	1.2	1.2	2012/0805	370	0.45	280	50	20
AWCU00201212501M02	2.0	1.2	1.2	2012/0805	500	0.55	170	50	20
AWCU00201212671M02	2.0	1.2	1.2	2012/0805	670	0.6	140	50	20
AWCU00201212901M02	2.0	1.2	1.2	2012/0805	900	0.6	80	50	20
AWCU00321619900M02	3.2	1.6	1.9	3216/1206	90	0.3	370	50	20
AWCU00321619121M02	3.2	1.6	1.9	3216/1206	120	0.3	370	50	20
AWCU00321619161M02	3.2	1.6	1.9	3216/1206	160	0.4	340	50	20
AWCU00321619221M02	3.2	1.6	1.9	3216/1206	220	0.4	320	50	20
AWCU00321619261M02	3.2	1.6	1.9	3216/1206	260	0.5	310	50	20
AWCU00321619601M02	3.2	1.6	1.9	3216/1206	600	0.8	260	50	20
AWCU00321619102M02	3.2	1.6	1.9	3216/1206	1000	1	230	50	20
AWCU00321619222M02	3.2	1.6	1.9	3216/1206	2200	1.2	200	50	20
AWCU00332523110XT2	3.3	2.5	2.3	3325/1210	300	0.4	300	80	20
AWCU00332525110XG0	3.3	2.5	2.5	3325/1210	300	0.4	300	80	20
AWCU00332523220XT2	3.3	2.5	2.3	3325/1210	500	0.5	250	80	20
AWCU00332525220XG0	3.3	2.5	2.5	3325/1210	500	0.5	250	80	20
AWCU00332523510XT2	3.3	2.5	2.3	3325/1210	1000	0.7	200	80	20
AWCU00332525510XG0	3.3	2.5	2.5	3325/1210	1000	0.7	200	80	20
AWCU00332523101XT2	3.3	2.5	2.3	3325/1210	2200	1.5	150	80	20
AWCU00332525101XG0	3.3	2.5	2.5	3325/1210	2200	1.5	150	80	20
AWCU00453228201XTE	4.5	3.2	2.8	4532/1812	200	4.5	100	50	20
AWCU00453226113TT2	4.5	3.2	2.6	4532/1812	300	0.6	250	50	20
AWCU00453226110XG0	4.5	3.2	2.6	4532/1812	670	0.5	360	50	20
AWCU00453226223TT2	4.5	3.2	2.6	4532/1812	500	1	200	50	20
AWCU00453226220XG0	4.5	3.2	2.6	4532/1812	1450	0.6	310	50	20
AWCU00453226513TT2	4.5	3.2	2.6	4532/1812	1000	1	200	50	20
AWCU00453226510XG0	4.5	3.2	2.6	4532/1812	3500	1	230	50	20
AWCU00453226104TT2	4.5	3.2	2.6	4532/1812	2000	2	150	50	20
AWCU00453226101XG0	4.5	3.2	2.6	4532/1812	6500	2	200	50	20

EMI-Common Mode Choke



Automotive for Signal Line

AWU000CMC-KIT JIS 2012, 3216, 3325, 4532 Size

Dimensions – Millimeters (Inches)

