



SPECIFICATIONS

PANEL SIZE	27"
PANEL RESOLUTION	3840 x 2160 (UHD)
REFRESH RATE	60Hz
RESPONSE TIME	4ms (GTG)
PANEL TYPE	IPS
BRIGHTNESS (NITS)	300 cd/m2
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
ADOBE RGB / DCI-P3 / SRGB	93%/98%/130%
ACTIVE DISPLAY AREA (MM)	596.736(H) x 335.664(V)
PIXEL PITCH (H X V)	0.1554(H) x 0.1554(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	1.07B
COLOR BIT	10 bits (8 bits + FRC)
HDR SUPPORT	HDR Ready
VIDEO PORTS	2x HDMI™ 2.0b (4K@60Hz) 1x DisplayPort (1.4a)
AUDIO PORTS	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2x 3W
VESA MOUNTING	75 x 75 mm
POWER TYPE	External Adaptor 12V 4A
POWER INPUT	100~240V, 50~60Hz
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	613.50 x 462.60 x 181.10 mm (24.15 x 18.21 x 7.13 inch)
CARTON DIMENSION (W X H X D)	697 x 458 x 119 mm (27.5 x 18.04 x 4.69 inch)
WEIGHT (NW / GW)	3.95 kg (8.71 lbs) / 6.2 kg (13.37 lbs)
CERTIFICATES	CB/CE Energy Star
VIDEO INPUT COMPATIBILITY	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
ACCESSORIES	1x 1.5M HDMI Cable (2.0b), 1x Power Cord, 1x Power Adaptor, 1x Quick Guide

FEATURES

- 4K UHD Resolution**
 Experience the incredibly sharp and crisp images, movies and gameplay etc., to meet your sensory needs.
- IPS Grade Panel**
 Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video
- EyesErgo**
 An eye care solution designed with ergonomics in mind.
- Wide Color Gamut**
 Game colors and details will look more realistic and refined, to push game immersion to its limits.
- Built-In Speaker**
 Built-in speakers allow you to listen clearly without connecting external speakers.
- Eye-Q Check**
 Help have self-check eyes & remind to take a rest while using the monitor for a long time.
- PIP / PBP Mode**
 PIP/PBP mode provide a better efficiency for creators when need it
- VESA Mountable**
 To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

Note

HDMI™ : 3840 x 2160 (Up to 60Hz)
DisplayPort: 3840 x 2160 (Up to 60Hz)
Adaptive Sync Support
HDMI™ CEC Support

*Adobe RGB, DCI-P3 and sRGB follow
CIE1976 Standard

CONNECTIONS

1. 2x HDMI™ (2.0b)
2. 1x DP (1.4a)
3. 1x Headphone-out
4. 1x DC Jack 1x Kensington Lock
5. OSD Button