

## UIC 558 13PIN SOCKET DUMMY KIT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 013 1014
Specification	UIC 558 13PIN SOCKET DUMMY KIT
HARTING eCatalogue	<a href="https://b2b.harting.com/09580131014">https://b2b.harting.com/09580131014</a>

### Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC 558
Element	Connector sets
Specification	Dummy kit

### Version

Termination method	Crimp termination
Gender	Female

### Technical characteristics

Insulation resistance	$>10^7 \Omega$
Tightening torque	5 Nm Fixing screws M6
Limiting temperature	-50 ... +125 °C
Mating cycles	$\geq 10,000$
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition IP67 unmated condition & cover closed

### Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated



Pushing Performance  
Since 1945

## Material properties

Colour (hood/housing)	RAL 7035 (light grey)
Material (seal)	Silicone
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

## Commercial data

Packaging size	1
Net weight	589 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140190184
ETIM	EC002635
eCl@ss	27440115 Circular connector (set)