

UIC 558 18PIN SOCKET DUMMY KIT



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 58 018 1014 |
| Specification | UIC 558 18PIN SOCKET DUMMY KIT |
| HARTING eCatalogue | https://b2b.harting.com/09580181014 |

Identification

| | |
|----------------|----------------|
| Category | Connector sets |
| Series | HARTING UIC |
| Identification | UIC 558 |
| Element | Connector sets |
| Specification | Dummy kit |

Version

| | |
|--------------------|-------------------|
| Termination method | Crimp termination |
| Gender | Female |

Technical characteristics

| | |
|--|---|
| Insulation resistance | $>10^7 \Omega$ |
| Tightening torque | 5 Nm Fixing screws M6 |
| Limiting temperature | -50 ... +125 °C |
| Mating cycles | $\geq 10,000$ |
| Degree of protection acc. to IEC 60529 | IP69 / IPX9K acc. to ISO 20653 mated condition IP67 unmated condition & cover closed |

Material properties

| | |
|-------------------------|---|
| Material (insert) | Polyamide (PA) |
| Colour (insert) | Black |
| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
| Surface (hood/housing) | Powder-coated |



Pushing Performance
Since 1945

Material properties

| | |
|---|---|
| Colour (hood/housing) | RAL 7035 (light grey) RAL 3020 (traffic red) |
| Material (seal) | Silicone |
| Material (locking) | Stainless steel |
| Material flammability class acc. to UL 94 | V-0 |

Specifications and approvals

| | |
|----------------|---|
| Specifications | UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529 |
|----------------|---|

Commercial data

| | |
|--------------------------------|-----------------------------------|
| Packaging size | 1 |
| Net weight | 690 g |
| Country of origin | India |
| European customs tariff number | 85366990 |
| GTIN | 5713140190283 |
| ETIM | EC002635 |
| eCl@ss | 27440115 Circular connector (set) |