

Overview	All product units ▼
Product unit	Passive Components ▼
Product group	Capacitors ▼
Product family	Design Kits for Capacitors ▼
Product family	Aluminum Polymer Capacitors ▼
Product family	Radial THT ▼
Design kit	Design Kit WCAP-PTHR Aluminum Polymer Capacitors ▼
 COMPONENTS  LOGIN 	

Low ESR & High Voltage 105 °C | Order Code 870055



Applications

- Low ripple voltage at the switching converter
 - Filtering
 - Smoothing
 - Coupling
- e.g. High-end power supply, industrial computer, VGA card, charger, digital set-top box

Download inlay 

Order Design Kit 

Products

870055673001

10 μ F, 35 V (DC), 2100 mA, 6.3 mm, 8 mm, 2.5 mm



SPEC



COMPONENTS



LOGIN

**870055673002**22 μ F, 35 V (DC), 2100 mA, 6.3 mm, 8 mm, 2.5 mm**870055874002**22 μ F, 63 V (DC), 1400 mA, 8 mm, 11.5 mm, 3.5 mm**870055674003**33 μ F, 35 V (DC), 2500 mA, 8 mm, 8 mm, 3.5 mm**870055875003**33 μ F, 63 V (DC), 1600 mA, 10 mm, 12.5 mm, 5 mm**870055875004**39 μ F, 63 V (DC), 1600 mA, 10 mm, 12.5 mm, 5 mm**870055674005**47 μ F, 35 V (DC), 2890 mA, 8 mm, 11.5 mm, 3.5 mm**870055875005**47 μ F, 63 V (DC), 1600 mA, 10 mm, 12.5 mm, 5 mm**870055875006**56 μ F, 63 V (DC), 1600 mA, 10 mm, 12.5 mm, 5 mm

COMPONENTS



LOGIN

Learn more**870055775007**68 μ F, 50 V (DC), 2000 mA, 10 mm, 12.5 mm, 5 mm

■ The capacitor product portfolio and



information about the latest products

87005567500882 μ F, 50 V (DC), 3700 mA, 10 mm, 12.5 mm, 5 mm**870055675009**100 μ F, 35 V (DC), 3700 mA, 10 mm, 12.5 mm, 5 mm**870055675010****Products & More**

Components

PCBs

Intelligent Systems

Newsletter

Career

Career Area

Interesting

Sustainability

Company

News Center

Events

Important

Support

Quality

Terms and Conditions

Compliance

**COMPONENTS**

LOGIN