

SD50P300WKQP

SD50 STATUS DISPLAY





SD50 Status Display with IO-Link; 8 x 96 pixels
 White Display LEDs; RGB indicator LEDs
 300 mm length; Polycarbonate; 18-30 V dc
 150 mm (6 in) 4-pin M12 PVC Pigtail QD
 Part Number: 817045

CERTIFICATIONS



ACCESSORIES TO COMPLETE YOUR SYSTEM

Add all or individual items to your cart. More options available below.

	<p>BC-M12F4-M12M4-22-1</p> <p>Cordset: Double Ended M12 4-pin Straight Female; 4-pin Straight Male Connectors 1 m (3.28 ft) 4x22 Black PVC Jacket Nickel-Plated Brass Coupling Nuts</p>
	<p>LMBSD50</p> <p>Bracket: For Use with SD50 Contains 2 Brackets and Screws</p>

SPECIFICATIONS

Power	DC
IP Rating	IP65
Display	Yes
Ships with Battery	No
Primary Housing Material	Polycarbonate
Indication	Yes
Color Input Control	Multiple (One or more wires/color, enables more colors than input wires)
Number of Colors	14
Product Size (mm)	50
Color Technology	RGB Configurable

Color Option 1	White
Animation Option 1	Programmable
Connection	Integral QD
Quick Disconnect Type	M12
Wire Selectable Function	Programmable
Number of Input Pins/Conductors	5
Array Length (mm)	300
Physical Dimensions (LxWxH or DxH mm)	325x50x28
High Temperature (up to 100° C)	60
Min Op. Temperature (°C)	-20
Storage Temp (°C)	-40 to 70
Primary Housing Color	Black
Primary Window Material	Polycarbonate
Feature: Washdown Rated	Yes
IO Link	Yes

COMPATIBLE PRODUCTS

DOUBLE-ENDED CORDSETS

	<p>BC-M12F4-M12M4-22-1</p> <p>Cordset: Double Ended M12 4-pin Straight Female; 4-pin Straight Male Connectors 1 m (3.28 ft) 4x22 Black PVC Jacket Nickel-Plated Brass Coupling Nuts</p>
	<p>BC-M12F4-M12M4-22-10</p> <p>Cordset: Double Ended M12 4-pin Straight Female; 4-pin Straight Male Connectors 10 m (32.8 ft) 4x22 Black PVC Jacket Nickel-Plated Brass Coupling Nuts</p>
	<p>BC-M12F4-M12M4-22-15</p> <p>Cordset: Double Ended M12 4-pin Straight Female; 4-pin Straight Male Connectors 15 m (49.2 ft) 4x22 Black PVC Jacket Nickel-Plated Brass Coupling Nuts</p>
	<p>BC-M12F4-M12M4-22-2</p> <p>Cordset: Double Ended M12 4-pin Straight Female; 4-pin Straight Male Connectors 2 m (6.56 ft) 4x22 Black PVC Jacket Nickel-Plated Brass Coupling Nuts</p>

	<p>BC-M12F4-M12M4-22-5</p> <p>Cordset: Double Ended M12 4-pin Straight Female; 4-pin Straight Male Connectors 5 m (16.4 ft) 4x22 Black PVC Jacket Nickel-Plated Brass Coupling Nuts</p>
	<p>LMBSD50</p> <p>Bracket: For Use with SD50 Contains 2 Brackets and Screws</p>
	<p>LMBSD50-180S</p> <p>Bracket: For Use with SD50 180 Degree Rotation Set of Two Stainless Steel</p>
	<p>LMBSD50-180SMAG</p> <p>Bracket: For Use with SD50 180 Degree Rotation; Stainless Steel Magnetic Mounting Kit Set of Two Up to 16 lb Pull</p>
	<p>LMBSD50MAG</p> <p>Bracket: For Use with SD50 Magnetic Mounting Kit Set of Two Up to 16 lb Pull</p>