

# Product Specification PDF

Date	Correct as of 6th Aug 2019
Brand	C.K
Product	T3887
Description	Ecotronic ESD Side Cutters
Barcode	5013969938876
Commodity code	8203200000
Country of origin	TW



Features & Benefits	Precision side cutters for fine cutting applications Suitable for cutting soft copper wires of up to 1.6mmØ / 14AWG Sharp, precision ground cutting edges with a full flush cut Special tool steel blade, hardened for long-term cutting performance Electro-static discharging handles ~ dissipative 10 <sup>9</sup> Contoured, dual component handle design for comfortable working Black oxidised finish for corrosion resistance and reduced glare Smooth-action return spring for convenience during repetitive work Joint with durable stainless steel rivet Technical information: Total length: 136 mm Blade length: 10 mm Cutting angle: 21° Head Height (from joint to tip): 21 mm Head Width (Widest point): 12 mm Steel Thickness: 3 mm Cutting Capacity (Copper only) : 1,6 mm / 14 AWG
Applicable Standards	IEC 61340 5.1 & 5.2
Health & Safety	None applicable
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	120
Width mm	139	220	21.6	240
Depth mm	70	80	8.4	460
Height mm	20	2.5	10.8	420
Weight	83	98	657	14.2
Packaging Information	Card use	0	Box	Case
	Card gms	0	69	1012.5
	Plastic use	Blister	0	-
	Plastic gms	15	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0