

# Product Specification PDF

|                   |                                    |
|-------------------|------------------------------------|
| Date              | <b>Correct as of 6th Aug 2019</b>  |
| Brand             | <b>C.K</b>                         |
| Product           | <b>T4845 26</b>                    |
| Description       | <b>Xonic Ceramic Trimmer 2.6mm</b> |
| Barcode           | <b>5013969882506</b>               |
| Commodity code    | <b>8205400000</b>                  |
| Country of origin | <b>DE</b>                          |



## Features & Benefits

~ Zirconia ceramic tips ~ safe trimming of highly sensitive electrical components ~ No electromagnetic induction  
 ~ No eddy current loss in HF (high frequency) ~ 100 % electric insulation ~ 100 % non-magnetic ~ 100 % non-static  
 ~ Unequalled resistance to wear □ 10 x better than metal / 100 x better than plastic ~ Total heat resistance of blades up to 1000°C ~ Extremely low thermal conductivity ~ 100 % rustproof ~ Highly resistant to all strong acids ( other than Hydrofluoric) ~ Anti-stick surface to prevent solder, soft or silverm to adhere to surfaces ~ Contamination free blades make them suitable for clean-rooms ~ Blade width: 2,6 mm ~ Blade thickness: 0,4 mm ~ Visible blade length: 15 mm ~ Overall length: 100 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

|                       | Product only | Product & primary packaging | Secondary packaging | Transit packaging |
|-----------------------|--------------|-----------------------------|---------------------|-------------------|
| Item Quantity         | 1            | 1                           | 10                  | 240               |
| Width mm              | 12           | 70                          | 130                 | 460               |
| Depth mm              | 12           | 20                          | 245                 | 300               |
| Height mm             | 110          | 210                         | 70                  | 260               |
| Weight                | 6            | 20                          | 285                 | 7.6               |
| Packaging Information | Card use     | Card                        | Box                 | Case              |
|                       | Card gms     | 6                           | 85                  | 787.5             |
|                       | Plastic use  | Blister                     | 0                   | -                 |
|                       | Plastic gms  | 8                           | 0                   | 0                 |
|                       | Metal use    | 0                           | 0                   | -                 |
|                       | Metal gms    | 0                           | 0                   | 0                 |
|                       | Timber use   | 0                           | 0                   | -                 |
|                       | Timber gms   | 0                           | 0                   | 0                 |