



SPECIFICATIONS

Panel Size	27" (69 cm)
Active Display Area (mm)	596.736(H) x 335.664(V)
Curvature	Curve 1500R
Panel Type	Rapid VA
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H) x 0.2331(V)
Aspect Ratio	16:9
Brightness (nits)	300 (Typ.)
Contrast Ratio	5000:1 (Typ.)
DCR	100000000:1
Signal Frequency	70.56KHz-266.4KHz / 48Hz-180Hz
ACTIVATED RANGE	48~180Hz
Refresh Rate	180Hz
Response time	0.5ms (GtG, Min.)
DYNAMIC REFRESH RATE TECHNOLOGY	AMD FreeSync™
HDR Support	HDR Ready
Video ports	1 x DisplayPort (1.4) 2 x HDMI™ (2.0b)
USB ports	N/A
Audio ports	1 x Headphone Out
Viewing Angle	178° (H) / 178° (V)
Adobe RGB / DCI-P3 / sRGB	80% / 80% / 105%
Surface Treatment	Anti-glare
Display Colors	1.07B , 10 bits (8 bits + FRC)
Frameless Design	Yes
PIP / PBP Function	N/A
Power Type	Power Cable
Power Input	100 ~ 240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A
Adjustment (Height)	N/A
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Weight (NW / GW)	3.95kg / 5.65kg
Dimension (W x D x H)	610 x 250 x 451.6 mm 610 x 90.4 x 362.5 mm(without stand)

FEATURES



Rapid VA Panel

Make sure the intensity and purity of colors when gaming.



1500R

Enjoy the most immersive gameplay with 1500R curvature rate.



180Hz High Refresh Rate

Experience smooth gaming with a blazing fast 180Hz refresh rate, that gives you the upperhand in fast moving games.



0.5ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 0.5ms response time.



HDR Ready

Provide eye-catching detail through contrast and shadows adjustment.



Console Mode

Perfectly support 120Hz at QHD 2K resolution with next-gen console like PS5 and Xbox series X/S.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.

Carton Dimension (W X D X H)

WW carton: 684 x 158 x 475 mm
Outer: 704 x 178 x 508 mm

Note

Display Port: 2560x1440 (Up to 180Hz)
HDMI™ 2.0: 2560x1440 (Up to 144Hz)

*Adobe RGB, DCI-P3 and sRGB follow
CIE1976 Standard

CONNECTIONS



1. 5-Way Joystick Navigator
2. 2 x HDMI™ (2.0b)
3. DisplayPort (1.4)
4. Headphone out
5. AC-in
6. Kensington Lock