

[Home](#) | [RF Antennas](#) | [Embedded Antennas](#) | RF Antenna Embedded LoRa Chip 915MHz

RF Antenna Embedded LoRa Chip 915MHz

ST0643-00-N02-A

Find In Stock & Buy Now

915MHz LoRa, IoT, ISM, LPWAN

 [Add To Parts List](#)  [Add To Compare](#)

Product Compliance

- RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)
- California residents see [Prop 65 Warning](#)

[Contact Us](#)

- Additional compliance information is available in our [Compliance Center](#).

[Contact Us](#)

Description



Passive 915MHz LoRa, IoT, ISM, LPWAN 50 Ohms

Downloads

 [Antenna Solutions Overview \(Size: 167 kb\)](#)

 [ST0643-00-N02-A PDF Customer Drawing \(Size: 995 kb \)](#) 

 [RF Antenna Solutions Guide \(Size: 2765 kb\)](#)

Product Life Cycle

Part Status	Active
-------------	--------

Product Specifications

Antenna Connector Type	PCB Mount	Contact Us
Antenna Wireless Application	LoRa	
Band Type	Single Band	
Center Frequencies	915MHz	
Electrical Type	Monopole	

Export Control Classification Number	EAR99	Contact Us
Frequency (Max GHz)	0.919	
IP Rating	Not Rated	
Impedance (Ohms)	50	
Mechanical Style	Chip	
Mil Qualified	Not Mil Qualified	
Number of Bands	1	
Physical Style	Ceramic	
Power (Max Watts)	1	
Temp (Max Degrees Celsius)	70	

**Temp (Min Degrees
Celsius)**

25

Contact Us

Copyright © 2020 Amphenol RF. All Rights Reserved.

[Copyright](#) | [Terms & Conditions of Sale](#) | [Privacy Policy](#) | [User Agreement](#) | [Logos](#) | [Amphenol.com](#)