

[Home](#) | [RF Antennas](#) | [Embedded Antennas](#) | [Chip Antenna GPS 1560-1590 MHz](#)

Chip Antenna GPS 1560-1590 MHz

ST0543-00-N08-U

[Find In Stock & Buy Now](#)

Chip Antenna, 1560-1590 MHz GPS, GPS

[!\[\]\(003082e50e3009141f59bd5df831749f_img.jpg\) Add To Parts List](#) [!\[\]\(f439ede8735757e3190eab35e168f1de_img.jpg\) Add To Compare](#)

Product Compliance

- RoHS (EU). Compliant with Exemption 6C - [View Certificate](#)
- California residents see [Prop 65 Warning](#)

[Contact Us](#)

- Additional compliance information is available in our [Compliance Center](#).




Description



Passive Chip Antenna, 1560-1590 MHz GPS, GPS, 50 Ohms

Downloads

 [ST0543-00-N08-U PDF Customer Drawing \(Size: 1035 kb\)](#) 

 [RF Antenna Solutions Guide \(Size: 2765 kb\)](#)

Product Life Cycle

Part Status	Active
--------------------	--------

Product Specifications

Antenna Connector Type	PCB Mount
Antenna Wireless Application	GPS
Band Type	Single Band
Center Frequencies	1575.42MHz
Electrical Type	Chip

[Contact Us](#)

Export Control Classification Number	EAR99
Frequency (Max GHz)	1.59
IP Rating	Not Rated
Impedance (Ohms)	50
Mechanical Style	Chip
Mil Qualified	Not Mil Qualified
Number of Bands	1
Physical Style	Ceramic
Power (Max Watts)	1
Temp (Max Degrees Celsius)	70

Contact Us

**Temp (Min Degrees
Celsius)**

25

[Contact Us](#)

Copyright © 2020 Amphenol RF. All Rights Reserved.

[Copyright](#) | [Terms & Conditions of Sale](#) | [Privacy Policy](#) | [User Agreement](#) | [Logos](#) | [Amphenol.com](#)