



Cw-75

CD & DVD inscription printer with integrated keyboard and US B interface.

General data:

CD-r title printer with inserted key board

Display: 12 indications, 4 lines

Pressure system: Thermal transfer

Print head: 200 x dpi

Pressure range: 74mm x 16mm

Print rate: 9mm/Sek.(schwarz)

Writings: 6 inserted writings plus each writing available over the PC

internal storage capacity: 4000 indications

Connection: USB

Current supply: 8 x battery type AA or line operation (optional) with the power pack Ad-a12280I

Dimensions: 76 x 184 x 185 mm (H x B x T)

Weight: 900 g

Prints on CD's and DVD's with free, unlined surface,

- no printable Ink jet CD's or DVD's uses -



- 43343 CD-r, 700 MT, 48-fach, 50's spindle



- 43337 CD-r, 700 MT, 48-fach, 50's spindle

For the use with Cw-75 recommended DVD



DVD + R

- 275521,00 DVD+R 47 4CX 1PK DATA/CVideo 03



- 275522.00
DVD+R 47 4CX CMX 5PK
DATA/CVideo



- 275524.00
DVD+R 47 25S 4X
DATA/CVideo 03

- 275466,01 DVD+R VIDEO 120 4CX LIBCASE TF

DVD - R

- 275517,00 Dvd r 47 4X 1PK DATA/CVideo 03



- 275518.00
Dvd r 47 4X CMX 5PK
DATA/CVideo



- 275520.00
Dvd r 47 25S 4X
DATA/CVideo 03

- 275467,01 Dvd r VIDEO 120 4X LIBCASE TF

Accessories:

Ribbon Tr-18bk-w-ej (black)

Ribbon Tr-18rd-w-ej (red)

Ribbon Tr-18bu-w-ej (blue)

Ribbon Tr-18sr-w-ej (silver)