RECHARGEABLE ACCU



Benefits

Great Value!

Charges Both AA & AAA NIMH Cells
Simple and Easy to Use with Convenient Wall Plug-In

Features

LED Indicator

- Red = Charging
- •Green = complete or trickle charge
- •Flashing Red = error abnormal battery or temperature

Available SKU's

- No Cells
- •2x HR6/AA (1800mAh)
- •4x HR6/AA Cells (1800mAh)
- •4x HR03/AAA Cells (900mAh)

Maintenance Charge Keeps Cells Fresh Charges in Six Hours*

Safety

Charge Termination Based on Temperature, and/or Built-In Timer

•Over temperature shutoff - prevents overheat of cell

Design

International Charge Capability – device can be used worldwide (with suitable converter plug)

Primary plug matches local requirements

Packaging with Clear Device Linkage, Leveraging Duracell Heritage

Technical

Battery Charger	Class 2, integral Power Supply
Plug	Direct Plug-In Matches Local Requirements
Battery Type	NiMH HR6/AA or HR03/AAA
Battery Fit	2 or 4 NiMH AA/HR6, 2 NiMH AAA/HR03
Input	100-240V AC, 50-60 Hz
Output	HR6/AA: 5.6V DC 0.36A HR03/AAA: 2.8V DC 0.16A
Operating Temperature	0° C – 40° C (32° F – 103° F)
Dimensions	120mm (L) x 80mm (W) x 34mm (H)



Berkshire Corporate Park Bethel, CT 06801 U.S.A. Telephone Toll-free: (Global) 1-203-796-4500 Internet: www.duracell.com