



**TL030AB16**

**AlN Flangeless Termination**

**Power: 30 Watts (CW)**

**Resistance: 50  $\Omega$   $\pm$  5%**

**VSWR: 1.07:1**


**Frequency Range: DC to 2.3 GHz**

**Substrate: AlN**



### TYPICAL PERFORMANCE


#### VSWR



For detailed information regarding this product or sample request contact Johanson Sales



Johanson Manufacturing Corporation • 301 Rockaway Valley Road, Boonton, New Jersey 07005 • Phone 973.334.2676 • Fax 973.334.2954  
STAY TUNED • ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION • [WWW.JOHANSONMFG.COM](http://WWW.JOHANSONMFG.COM)



For detailed information regarding this product or sample request contact Johanson Sales