




[Back](#)

Selected Cable: 17505				
End View	Plug	Cord	Connector	End View
5-15P	173	SJT	386E	C13

<b>Part Number</b>	17505
<b>Category</b>	3 conductor plastic detachable
<b>Shielding</b>	unshielded
<b>Jacket Color</b>	black
<b>Length Feet</b>	9'10"
<b>Length Meters</b>	3
<b>Temperature Rating</b>	60 C°C
<b>Packaging Units Per Carton</b>	H-50, H-25
<b>Color Coding</b>	International
<b>AWG Stranding</b>	14 (41x30)
<b>Nominal OD Inch</b>	0.38
<b>Nominal OD millimeter</b>	9.65
<b>Rating</b>	1875 Watts 15-125V
<b>Notes</b>	See 17504 for 6'7" version. See 17605 for shielded version.

**Cord View**



**Approvals**



Qty:

Back

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

